



44100 SERIES

Thermistor Components

Teflon® sheathed epoxy encapsulated precision interchangeable NTC thermistor utilizing high stability pressed-disk ceramic sensor for use in harsh chemical environments. Sensor is protected by a 2" (51mm) Teflon® sheath for protection from harsh chemicals. One inner lead is sleeved with Teflon® tubing for insulation. A nickel stiffening wire allows shaping of the sheath.

Interchangeability

The term interchangeability refers to how accurately thermistors track a nominal resistance curve. In the case of a $\pm 0.2^{\circ}\text{C}$, through all portions of the interchangeable range, the part is within $\pm 0.2^{\circ}\text{C}$ of the nominal value for that part. This term is sometimes confused with accuracy. Keep in mind the $\pm 0.2^{\circ}\text{C}$ figure only refers to nominal curve; absolute accuracy for thermistor at a measured temperature is significantly better. Contact us directly if you require more information.

Features

- Teflon® Sheath for Hostile Environments
- 100 Ohm to 1 MEG Ohm Resistance @ 25°C
- Interchangeability $\pm 0.2^{\circ}\text{C}$, 0°C to 70°C
- Good Long Term Stability
- High Sensitivity
- Pressed Disk Ceramic Characteristics
- Thermally Conductive Epoxy Coating
- RoHS Compliance

Applications

- Harsh Chemical Environments
- Moderate Temperature Applications
- Tight Tolerance Applications
- General Applications Requiring Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments

Performance Specifications

	Model Number	Ordering Part Number	Zero Power Resistance ohm at 25°C	Beta 0- 50°C (K)	Ratio ohm 25/125°C	Maximum working temperature	Best storage and working temperature
±0.2°C Interchangeability Tolerance 0 – 70°C	44101	095311	100	2854	11.49	100°C	-80 + 50°C
	44102	095312	300	3118	15.15	100°C	-80 + 50°C
	44103	095313	1000	3271	17.33	100°C	-80 + 50°C
	44104	095403	2252	3891	29.26	150°C	-80 + 120°C
	44105	095404	3000	3891	29.26	150°C	-80 + 120°C
	44107	095406	5000	3891	29.26	150°C	-80 + 120°C
	44106	095405	10K	3574	23.51	150°C	-80 + 120°C
	44108	095407	30K	3810	29.15	150°C	-80 + 120°C
	44111	095408	100K	3988	34.82	150°C	-80 + 120°C
	44114	095409	300K	4276	46.02	150°C	-80 + 120°C
	44115	095410	1 meg	4582	61.96	150°C	-80 + 120°C

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[11031964-00](#)