




OBSOLETE-SUPERSEDED BY		104427-7	5	.884	.800	8	9	3-104427-0
OBSOLETE-SUPERSEDED BY		104427-6	5	.784	.700	7	8	2-104427-9
OBSOLETE-SUPERSEDED BY		104427-5	5	.684	.600	6	7	2-104427-8
7 OBSOLETE 7 OBSOLETE 7 OBSOLETE 7 OBSOLETE 7 SUPERCEDED BY 5-146288-6 7 SUPERCEDED BY 5-146288-5			5	3.984	3.900	39	40	2-104427-7
				3.484	3.400	34	35	2-104427-6
				2.984	2.900	29	30	2-104427-5
				2.584	2.500	25	26	2-104427-4
				2.484	2.400	24	25	2-104427-3
				2.384	2.300	23	24	2-104427-2
				2.284	2.200	22	23	2-104427-1
				2.184	2.100	21	22	2-104427-0
				2.084	2.000	20	21	1-104427-9
				1.984	1.900	19	20	1-104427-8
				1.884	1.800	18	19	1-104427-7
				1.784	1.700	17	18	1-104427-6
				1.684	1.600	16	17	1-104427-5
				1.584	1.500	15	16	1-104427-4
				1.484	1.400	14	15	1-104427-3
				1.384	1.300	13	14	1-104427-2
				1.284	1.200	12	13	1-104427-1
				1.184	1.100	11	12	1-104427-0
				1.084	1.000	10	11	1-104427-9
				.984	.900	9	10	1-104427-8
				.884	.800	8	9	104427-7
				.784	.700	7	8	104427-6
				.684	.600	6	7	1-104427-5
				.584	.500	5	6	1-104427-4
				.484	.400	4	5	1-104427-3
				.384	.300	3	4	104427-2
				.284	.200	2	3	104427-1
				REMARKS			C	B

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN H. MOLL	28JUN88	 TE Connectivity	
			CHK R. FEIDT	28JUN88		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. FEIDT	28JUN88	NAME HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE
		0 PLC ± —		PRODUCT SPEC		
		1 PLC ± —		—		
		2 PLC ± —		APPLICATION SPEC		
		3 PLC ± .005		—		SIZE A2
		4 PLC ± —		—		
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR—BLACK		FINISH POSTS: .000015 GOLD IN CONTACT AREA, .000100—, .000200 MATTE TIN—LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		WEIGHT —		DRAWING NO C-104427
				CUSTOMER DRAWING		
SCALE 4:1						SHEET 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104427-4](#)