

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REVISED PER ECO-11-023039		21FEB12	KH	MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2, BLACK.
TERMINAL: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC AND CHROMATE PLATED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 600V.
WIRE RANGE: 12 AWG MAX.

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C



- 1

WHITE INK MARKING, APPROX AS SHOWN.
- 2

NICKEL PLATED BRASS SCREW.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4

ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS



SEE FIGURE

3

 OBSOLETE

7.562	17	SSB7FP170201	1-1546972-7
7.125	16	SSB7FP16020111	9-796602-4
7.125	16	SSB7FP160201	1-1546972-6
6.687	15	SSB7FP150201	4-1437416-6
6.250	14	SSB7FP140203	1546561-4
6.250	14	SSB7FP140201	4-1437416-5
5.812	13	SSB7FP130201	4-1437416-3
5.375	12	SSB7FP120201	4-1437416-0
4.937	11	SSB7FP110201	1-1546972-1
4.500	10	SSB7FP100203	3-1437416-6
4.500	10	SSB7FP100201	3-1437416-4
4.062	9	SSB7FP090203	1-1546561-9
4.062	9	SSB7FP090201	1546972-9
3.625	8	SSB7FP08020111	1986330-3
3.625	8	SSB7FP080203	2-1437416-9
3.625	8	SSB7FP080201	1546972-8
3.187	7	SSB7FP070203	2-1437416-6
3.187	7	SSB7FP07020111	2-1437416-5
3.187	7	SSB7FP070201	2-1437416-4
2.750	6	SSB7FP06020111	1986330-2
2.750	6	SSB7FP060203	2-1437416-3
2.750	6	SSB7FP060201	2-1437416-1
2.312	5	SSB7FP050203	2-1546972-7
2.312	5	SSB7FP050201	1-1437416-5
1.875	4	SSB7FP04020111	1986330-1
1.875	4	SSB7FP040203	1-1437416-3
1.875	4	SSB7FP040201	1-1437416-1
1.437	3	SSB7FP030201	1437416-6
1.000	2	SSB7FP020201	1437416-2
DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 2/10/05	STE TE Connectivity			
DIMENSIONS: INCHES		CHK S YODER 2/10/05				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER 2/10/05	NAME			
		PRODUCT SPEC	SSB7FPXX0201			
		APPLICATION SPEC				
MATERIAL -	FINISH -	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-9-796602-2	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 2	REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

2

3

4

5

6

7

2-1437416-5

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

9-796602-4

1

2

3

4

5

6

7

8

1986330-3

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-5

1

2

3

4

1986330-1

1

2

3

4

5

6

1986330-2

2

11.937

27

SSB7FP270201

9-796602-2

11.500

26

SSB7FP260203

1-1546561-8

11.500

26

SSB7FP260201

2-1546972-6

11.062

25

SSB7FP250201

2-1546972-5

10.625

24

SSB7FP24020111

1986330-5

10.625

24

SSB7FP240201

2-1546972-4

10.187

23

SSB7FP230201

2-1546972-3

9.750

22

SSB7FP220201

2-1546972-2

9.312

21

SSB7FP210201

2-1546972-1

8.875

20

SSB7FP200201

2-1546972-0

8.437

19

SSB7FP190201

1-1546972-9

8.000

18

SSB7FP180201

1-1546972-8

DIM A

NO. OF POS.

CATALOG NUMBER

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

ANGLES

± 1°

FINISH

-

DWN

S SCHL GEL

2/10/05

CHK

S YODER

2/10/05

APVD

S YODER

2/10/05

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

SSB7FPXX0201

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-9-796602-2

-

SCALE

SHEET

REV

NTS

2 OF 2

A

1470-19

(3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSB7FP060203](#)