





COIL: @ 25°C  
 RESISTANCE 850 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 12.0 VDC  
 MUST OPERATE 7.0 VDC  
 MUST RELEASE 4.0 VDC MAX, 0.64 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX  
RELEASE TIME 2.0 MS MAX  
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/7/97 8/7/97

**COMMUNICATIONS  
INSTRUMENTS, INC.**

CUST. QPL  
 CUST. NO. M39016/11-035L

TYPE 'JMS' RELAY

**JMSC-12XL**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39016/11-035L](#)