



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**  
Die Sets Type: **Removable/Interchangeable**  
Specification Type: **MIL Spec, TE Product Specification (114-)**  
TE Certification: **Yes – Certificate Included**  
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content















Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-AM74-AM74A AMPOWER TERMINAL 1 STUD HOLE</p>	 <p>TE Part # 53680-2 TERMINAL,LNG BBL AMPOWER 1/0</p>	 <p>TE Part # 1490747-1 HYP10 HEAVY DUTY 12T HEAD</p>	 <p>TE Part # CAT-AM74-AM74B AMPOWER TERMINAL 2 STUD HOLES</p>
 <p>TE Part # 324458 SPLICE,AMPOWER BUTT 1/0</p>	 <p>TE Part # 324443 SPLICE,AMPOWER PARA 1/0</p>	 <p>TE Part # CAT-AM74-AM74 AMPOWER TERMINAL WO STUD HOLE</p>	 <p>TE Part # 325318 TERMINAL,AMPOWER 1/0 0</p>
 <p>TE Part # 325320 TERMINAL,AMPOWER BENT 1/0</p>	 <p>TE Part # 1490749-1 HYP10 8-4/0AWG MANUAL TOOL</p>	 <p>TE Part # 194037-2 SKT ASSY,9MM,1/0 GAGE</p>	 <p>TE Part # 1490745-1 HYP10 LIGHT DUTY 12T HEAD</p>






TE Part # 1490746-1  
HYP10 LIGHT DUTY 14T HEAD



TE Part # 193837-7  
PIN ASSY.,CRIMP, 8MM,1/0AWG



TE Part # 326800-8  
TERM,AMPOWER 1/0 3/8 UNPL

Customers Also Bought



TE Part #36203  
TERMINAL,PIDG R 16-14HD 1/2




TE Part #53434-1  
AMPOWER QUICK DISC 400MCM



TE Part #1478762-9  
METAL BACKSHELL 9 WAY TOP E



TE Part #201501-1  
SPIROL PIN



TE Part #326800  
TERMINAL,AMPOWER 1/0 3/8



TE Part #DT06-12SA-EP08  
PLG, 12P, BLK, N, SEAL RET,ENH KEY, CAP,A



TE Part #1804700-2  
HYP10 220V HEAVY DUTY ELECTRIC PUMP



TE Part #1901775-1  
HYP10 7FT HAND CTRL



TE Part #1490745-1  
HYP10 LIGHT DUTY 12T HEAD

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies



English

Instruction Sheets

Instruction Sheet (U.S.)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1583095-1](#)