



Heat Shrink Tubing > Single Thin Wall DR 25 TW Heat Shrink Tubing 2:1 Shrink Ratio



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **9.5 mm [.374 in]**

Recovered Inside Diameter (Max): **4.8 mm [.189 in]**

Shrink Ratio: **2:1**

[All Single Thin Wall DR 25 TW Heat Shrink Tubing 2:1 Shrink Ratio \(10\)](#)

Features

Product Type Features

Wall Type	Single
-----------	--------

Body Features

Material Systems Code	25
Fluid Type	Aviation Fuel, Brake Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Crosslinked Elastomer
Flexibility	Very Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.64 mm[.025 in]
Expanded Inside Diameter (Min)	9.5 mm[.374 in]
Recovered Inside Diameter (Max)	4.8 mm[.189 in]
Heat Shrink Tubing Size Range	4.8 – 9.5 mm[.189 – .374 in]

Usage Conditions

Shrink Temperature (Min)	150 °C
Fluid Resistance	Splash Protection



Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-75 – 150 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
Recovery Temperature	175 °C

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Packaging Features

Packaging Method	Spool
------------------	-------

Other

Product Source	US
----------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought



TE Part #6458864001
Single Thin Wall DR 25 TW Heat Shrink
Tubing 2:1 Shrink Ratio



TE Part #66507-2
PIN CONTACT,20DF




TE Part #696453-000
B-053-70



TE Part #696437-000
B-051-00-01



TE Part #5-147323-8
09 MTE HDR SRRA SMT.100CL



TE Part #391903-000
D-602-0146



TE Part #ZPF000000000007108
9602-04H 14-19 PN

Documents

Product Drawings

[DR-25-TW-3/8-0-SP](#)

English

[DR-25-TW-3/8-0-SP](#)

English

Datasheets & Catalog Pages

[1654025_Sec3_DR-25-TW](#)

English

[6-1773439-3TubingSelectionGuideEN](#)

English

Product Specifications

[DR-25-TW SLEEVING](#)

English

[Product Specification](#)

English



Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1197060-5](#)