




Raychem

TE Internal #: 971078-000

Cable Transitions & Breakouts, Y Shape, 3 Branches , 25, 25,  
Adhesive Precoat Adhesive Requirement

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**

Number of Branches & Legs: **3**

Material Code: **25**

Material Systems Code: **25**

Adhesive Requirement: **Adhesive Precoat**

## Features

### Product Type Features

Molded Part Shape	Y Shape
Size Code	023

### Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Precoat

### Body Features

Material	Fluid Resistant Modified Elastomer
Material Code	25
Material Systems Code	25

### Dimensions

Inside Diameter Range (Leg 2)	6.1 – 13.2 mm [.24 – .52 in]
Inside Diameter Range (Body)	12.4 – 26.9 mm [.49 – 1.06 in]
Inside Diameter Range (Leg 1)	6.1 – 13.2 mm [.24 – .52 in]

### Usage Conditions

Operating Temperature Range	-75 – 150 °C [-103 – 302 °F]
-----------------------------	------------------------------

### Operation/Application

Power Cable Accessory	No
-----------------------	----

### Industry Standards



Government Qualified	No
----------------------	----

### Other

Adhesive Code	225
---------------	-----

Molded Part Shape Code	382A
------------------------	------

Fluid & Chemical Resistance	Long-Term Exposure at High Temperature
-----------------------------	----------------------------------------

Adhesive Options	/225 Precoat
------------------	--------------

Comment	Use only with DR-25 tubing.
---------	-----------------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
----------------------------------------	-------------------------------------------------------------------------------------------------------------------------------

Halogen Content	Out of Scope - excluded from Halogen requirements
-----------------	---------------------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	----------------------------------------------

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CJ2087-000  
HL2010E-KIT-120V


## Customers Also Bought




TE Part #223494-000  
202K153-25/225-0



TE Part #117451-000  
Bulbous Heat Shrink Boots: Lipped,  
Right Angle




TE Part #153282-000  
342A012-25/225-0



TE Part #164153-000  
301A022-25/225-0



TE Part #A165103001  
RAY-101-7.5(100)



TE Part #2831443005  
44A0111-18-2L



TE Part #2266428-1  
OCEAN\_2.0\_Applicator-S-063F079F



TE Part #0059013002  
RAY-101-20.0(50)

## Documents

### Product Drawings

[382A023-25/225-0](#)

English

### Datasheets & Catalog Pages

[1654025\\_Sec4\\_-25](#)

English

### Raychem Molded Parts Visual Guide

English

### Product Specifications

[Product Specification](#)

English

### Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)



[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[382A023-25/225-0](#)