

| LOC | DIST | REVISIONS |     |                            |           |      |      |
|-----|------|-----------|-----|----------------------------|-----------|------|------|
|     |      | P         | LYR | DESCRIPTION                | DATE      | DWN  | APVD |
| DF  | -    | A         |     | RELEASED PER ECO-11-000354 | 12JAN2011 | RL   | RPW  |
|     |      | B         |     | REV PER ECO-11-011392      | 09JUN2011 | RJM3 | DM   |
|     |      |           |     |                            |           |      |      |

D

C

B

A

D

C

B

A

STRAIN RELIEF CLAMP  
THERMOPLASTIC  
PACKAGED UNASSEMBLED

#2-56 CAPTIVE SCREW  
STAINLESS STEEL  
QTY 4

WIRE TIE, SHOWN FOR REFERENCE ONLY  
CUSTOMER SUPPLIED

2.607  
REF

.296±.002

RECEPTACLE SHELL  
NICKEL PLATED  
ALUMINUM ALLOY

#4-40 JACKSCREW  
STAINLESS STEEL  
QTY 2


CONNECTOR KIT INCLUDES QUADRAX CONTACTS (TYCO PART# 1445692-3, QTY 4) FOR 100Ω CABLE.

2. RECOMMENDED CABLES :  
RAYCHEM, CEC-RWC-18687, CEC-RWC-18664  
TENSOLITE, NF24Q100, NF26Q100.


CONNECTOR IS MARKED WITH TYCO ELECTRONICS PART NUMBER, TYCO ELECTRONICS LOGO, CAGE CODE & DATE CODE.

4. OPERATING TEMPERATURE RANGE: -65°C TO 125°C (-85°F TO 257°F).

5. SILVER PLATED, STAINLESS STEEL RETENTION CLIPS ARE INSTALLED IN THE CONNECTOR.



INTERFACIAL SEAL  
FLUOROSILICONE



2000263-1

PART NUMBER

|  |  |                                 |  |  |  |  |
|--|--|---------------------------------|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>D. FABIAN<br>10MAY2007   | TE Connectivity  |  |  |  |
| DIMENSIONS:                            |  | CHK<br>R.P. WALTER<br>27OCT2009 |  |  |  |  |
| IN                                     |  | APVD<br>B. YOHN<br>28OCT2009    | NAME<br>KIT, RECTANGULAR QUADRAX 404<br>LOW PROFILE SIZE 3<br>RECEPTACLE |  |  |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | PRODUCT SPEC                    | SIZE   |  |  |  |
| 9 PLC ±.01                             |  | APPLICATION SPEC                | CAGE CODE  |  |  |  |
| 3 PLC ±.01                             |  | WEIGHT                          | DRAWING NO   |  |  |  |
| 5 PLC ±.005                            |  | CUSTOMER DRAWING                | A100779C=2000263   |  |  |  |
| 4 PLC ±.005                            |  | SCALE                           | 2:1  |  |  |  |
| ANGLES ±.1                             |  | SHEET                           | 1 OF 1   |  |  |  |
| FINISH                                 |  | REV                             | B  |  |  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2000263-1](#)