






Stecklänge / mating length



E = early mate, late break / voreilend



S = standard

L = late mate, early break / nacheilend



Elastische Einpresszone / compliant pressfit zone
Isolierwerkstoff / housing material : PBT GF 30
Bauart 4 / type 4
Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

- 1) $\phi 1,0^{+0,09}_{-0,06}$ Durchmesser des metallisierten Loches
 $\phi 1,0^{+0,09}_{-0,06}$ Diameter of finished plated-through hole

Dimension no.			Tolerances				Scale		2:1			
			ISO 8015		All Dimensions in mm		Material					
<u>Customer drawing:</u> All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.					Subject to modification without prior notice. Drawing will not be updated.			Messerleiste B/3 20 EE Male Connector B/3 20 pressfit				
								384278				
					ERNI International AG Zürichstrasse 72 8306 Brüttisellen - Zürich Switzerland							
b				05.10.2011				I				
Index				Date				A3				
Class								STVB/3				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[384278](#) [384278-E](#)