





NOTES:

- 1FOR USE ON MINIATURE APPLICATORS (LEFT–RIGHT FEED)
- 2HANDTOOL 180319 TO BE USED.
- 3APPLICATION SPEC. 114–19025.
- 4PRODUCT SPEC. 108–19084.
- REVERSE REELED FOR MINI APPLICATOR.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- TAB CUTOFF : 1.0 MAX



WIRE RANGE :
1,0 – 2,5 mm²
INSULATION RANGE :
2,5 – 3,8 mm DIA.

100689–4	TINPLATED	PH.BRONZE		1–100645–4	
100689–3	UNPLATED	PH.BRONZE		1–100645–3	
100689–2	TINPLATED	BRASS		1–100645–2	
100689–1	UNPLATED	BRASS		1–100645–1	
100689–4	TINPLATED	PH.BRONZE		100645–4	
100689–3	UNPLATED	PH.BRONZE		100645–3	
100689–2	TINPLATED	BRASS		100645–2	
100689–1	UNPLATED	BRASS		100645–1	
LOOSE PIECE 		FINISH		MATERIAL	
—	—	—	—	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED	
—	—	—	—		
B2	REVISED PER ECR–21–120358	SS	DH 03JUN2022		
B1	REVISED PER ECO–09–020932	KK	AEG 27AUG09	© COPYRIGHT 19 – BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION ,19	
B	EH–0935–93	P.B.	P.B. 03.12.93	 AMP HOLLAND B.V. 's–Hertogenbosch, The Netherlands.	
A	EH–0242–93	P.B.	P.B. 14.04.93		
0	H–9565	P.B.	A.B. 20.02.92		
LTR.	REVISION RECORD	DR.	CHK.	DATE	NAME LOW INSERTION FORCE FASTON RECEPTACLE FOR 0,8 mm TABTHICKNESS .250srs(6,3)
DR.:	P.BEIJNON	CHK.:	A.BIJNEN	APP.:	
DATE:	20.02.92	DATE:	–	DATE:	
APP.:		L.v.SOEST.		DWG.No.	REV.LTR.
				C–100645	B2
					SHEET
					1 OF 1
					A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-100645-3](#)