


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19AUG2021	AP	IG





TE INTERNAL PN	ALIAS PN	PLATING
1060-12-0144-PS	1060-12-0144-PS	Selective Ni, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-12-0166-PS	1060-12-0166-PS	Selective Ni, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-12-0222-PS	1060-12-0222-PS	Ni/Cu Overall

2. 100 TERMINALS PER STRIP

1. REFER TO PRODUCT DRAWINGS 1060-12-01XX AND 1060-12-02XX FOR PRODUCT DETAILS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. POLO 19AUG2021	 TE Connectivity					
DIMENSIONS: INCHES		CHK I. GRANTCHAROVA 19AUG2021						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD I. GRANTCHAROVA 19AUG2021	NAME STAMPED CONTACT PIN SIZE 12 PARTIAL STRIP				
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151000					
	MATERIAL		FINISH				APPLICATION SPEC 114-151002	
		WEIGHT	SIZE A3			CAGE CODE 00779	DRAWING NO C-1060-12-XXXX-PS	RESTRICTED TO -
CUSTOMER DRAWING					SCALE 5:1	SHEET 1	OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1060-12-0222-PS](#)