




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



8-1123723-3 SHOW

											27.72	29.12	31.62	NATURAL	8		7-1123723-8
														GREEN		6-1123723-8	
														BLACK		5-1123723-8	
														RED		4-1123723-8	
														BLUE		3-1123723-8	
														YELLOW		2-1123723-8	
														NATURAL		1-1123723-8	
											23.76	25.16	27.66	NATURAL	7		7-1123723-7
														GREEN		6-1123723-7	
														BLACK		5-1123723-7	
														RED		4-1123723-7	
														BLUE		3-1123723-7	
														YELLOW		2-1123723-7	
														NATURAL		1-1123723-7	
											19.80	21.20	23.70	NATURAL	6		7-1123723-6
														GREEN		6-1123723-6	
														BLACK		5-1123723-6	
														RED		4-1123723-6	
														BLUE		3-1123723-6	
														YELLOW		2-1123723-6	
														NATURAL		1-1123723-6	
											15.84	17.24	19.74	NATURAL	5		7-1123723-5
														GREEN		6-1123723-5	
														BLACK		5-1123723-5	
														RED		4-1123723-5	
														BLUE		3-1123723-5	
														YELLOW		2-1123723-5	
														NATURAL		1-1123723-5	
											11.88	13.28	15.78	NATURAL	4		7-1123723-4
														GREEN		6-1123723-4	
														BLACK		5-1123723-4	
														RED		4-1123723-4	
														BLUE		3-1123723-4	
														YELLOW		2-1123723-4	
														NATURAL		1-1123723-4	
											7.92	9.32	11.82	NATURAL	3		8-1123723-3
														NATURAL		7-1123723-3	
														GREEN		6-1123723-3	
														BLACK		5-1123723-3	
														RED		4-1123723-3	
														BLUE		3-1123723-3	
														YELLOW		2-1123723-3	
														NATURAL		1-1123723-3	
											3.96	5.36	7.86	NATURAL	2		7-1123723-2
														GREEN		6-1123723-2	
														BLACK		5-1123723-2	
														RED		4-1123723-2	
														BLUE		3-1123723-2	
														YELLOW		2-1123723-2	
														NATURAL		1-1123723-2	
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"REF	"A"REF	COLOR	POS	ASS'Y P/N	
											DIMENSION						

											39.60	41.00	43.50	NATURAL	11	<div>18</div> 8-1123723-1		
																	GREEN	6-1123723-1
																	BLACK	5-1123723-1
																	RED	4-1123723-1
																	BLUE	3-1123723-1
																	YELLOW	2-1123723-1
																	NATURAL	1-1123723-1
											35.64	37.04	39.54	NATURAL	10	<div>17</div> 7-1123723-0		
																	GREEN	6-1123723-0
																	BLACK	5-1123723-0
																	RED	4-1123723-0
																	BLUE	3-1123723-0
																	YELLOW	2-1123723-0
																	NATURAL	1-1123723-0
											31.68	33.08	35.58	NATURAL	<div>16</div> 7-1123723-9			
	X				X						39.60	41.00	43.50	NATURAL	9	7-1123723-1		
											31.68	33.08	35.58	GREEN		6-1123723-9		
																	BLACK	5-1123723-9
																	RED	4-1123723-9
																	BLUE	3-1123723-9
																	YELLOW	2-1123723-9
																	NATURAL	1-1123723-9
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N
PIN POSITION											DIMENSION				COLOR	POS	ASS'Y P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01 APVD Y.KASHIWA 13MAR'01		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ± 3°		3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY	
		PRODUCT SPEC 108-5609		SIZE A2 CAGE CODE 00779 DRAWING NO C-1123723 RESTRICTED TO —	
		APPLICATION SPEC 114-32134			
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —	
CUSTOMER DRAWING				SCALE N/A	
				SHEET 2 OF 2	
				REV AA5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1123723-2](#)