


P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA5	REVISED PER ECR-22-129998	12APR2022	WH	LC

- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO PINS MISSING.
- 6 PIN: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0(ONLY NATURAL COLOR).
- 8 ○ : WITH PIN,  
X : WITHOUT PIN.
- 10 SUPERSEDED BY 1744489-2.
- 11 SUPERSEDED BY 1744489-4.
- 12 SUPERSEDED BY 1744489-5.
- 13 SUPERSEDED BY 1744489-6.
- 14 SUPERSEDED BY 1744489-7.
- 15 SUPERSEDED BY 1744489-8.
- 16 SUPERSEDED BY 1744489-9.
- 17 SUPERSEDED BY 1-1744489-0.
- 18 SUPERSEDED BY 1-1744489-1.
- 19 VALUES FOR UL 61800-5-1, ONLY NATURAL COLOR.

Flam	RTIe deg C	HWI	HAI	CTI
V0	130	PLC 2	PLC 4	PLC 2_UL746

20 PRELIMINARY: NOT FOR PRODUCTION




2 FIG.1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01	TE Connectivity		
DIMENSIONS: mm		CHK M.SHINDO 13MAR'01			
		APVD Y.KASHIWA 13MAR'01	NAME		
		PRODUCT SPEC 108-5609	3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY		
MATERIAL SEE TABLE		APPLICATION SPEC 114-32134	SIZE A2	CAGE CODE 00779	DRAWING NO C=1123723
FINISH SEE TABLE		WEIGHT -	RESTRICTED TO -		REV AA5
CUSTOMER DRAWING			SCALE N/A	SHEET 1 OF 2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

													39.60	41.00	43.50	NATURAL	11	8-1123723-1		
																			GREEN	6-1123723-1
																			BLACK	5-1123723-1
																			RED	4-1123723-1
																			BLUE	3-1123723-1
																			YELLOW	2-1123723-1
																			NATURAL	1-1123723-1
													35.64	37.04	39.54	NATURAL	10	7-1123723-0		
																			GREEN	6-1123723-0
																			BLACK	5-1123723-0
																			RED	4-1123723-0
																			BLUE	3-1123723-0
																			YELLOW	2-1123723-0
																			NATURAL	1-1123723-0
													31.68	33.08	35.58	NATURAL	7-1123723-9			
		X				X														NATURAL
													31.68	33.08	35.58	GREEN	9	6-1123723-9		
																			BLACK	5-1123723-9
																			RED	4-1123723-9
																			BLUE	3-1123723-9
																			YELLOW	2-1123723-9
																			NATURAL	1-1123723-9
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N		
PIN POSITION											DIMENSION									



8-1123723-3 SHOW 

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01 APVD Y.KASHIWA 13MAR'01		 TE Connectivity	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ± 3°		3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY	
		PRODUCT SPEC 108-5609 APPLICATION SPEC 114-32134		SIZE	RESTRICTED TO
MATERIAL		FINISH		CAGE CODE	
SEE TABLE		SEE TABLE		DRAWING NO	
		WEIGHT		A2 00779	
		CUSTOMER DRAWING		SCALE	
				SHEET	
				REV	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1123723-3](#)