



REVISIONS

P	L/R	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECN-22-145274	20SEP2022	RZ	HL

TERMINATION STYLES

SOLDER TERMINATIONS

WIRE WRAP TERMINATIONS AND SOLDER TERMINATION

BURRHEIGHT MAX 0,02
RADIUS OF EDGS MAX 0,05

		L	CODE
	SOLDER	2,9±0,3 3,7±0,3 4,5±0,3 6±0,3	01 05 02 03
	SOLDER	7,3±0,3	04
	WIRE WRAP	13±0,5	40
	SOLDER HOOKS	5,5±0,3 10±0,5	30
	SOLDER LUGS	5,5±0,3 10-0,5	35
	SOLDER RIGHT ANGLE	1,55-0,4	00
	SOLDER RIGHT ANGLE	3-0,4	10
	WITH MOUNTING BRACKET		
		13±0,5 17±0,5 4±0,5 13±0,5 17±0,5 6±0,5 6±0,5	60 61 63 66 67 69 70

TERMINATION WITH SN

SOLDER HOOKS

SOLDER LUGS

V 4 2 2 5 4 - * 2 * * * - + * * *

B : STANDARD VERSION
F : VERSION WITH FLUX-TIGHT COATING

CODE FOR PERFORMANCE LEVEL

CODE FOR TERMINATION STYLE

STYLE, NO OF CONTACTS
AND CONTACT ASSIGNMENT
SEE PAGE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN CUYVELIER 14FEB89

CHK -

APVD -

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SIZE A1

CAGE CODE 00779

DRAWING NO 1393640-1

RESTRICTED TO

SCALE NTS

SHEET 1 OF 2

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1393641-4](#)