








Sin nuestra expresa autorización, queda terminantemente prohibida la reproducción total o parcial de este documento, así como su uso indebido y/o su exhibición o comunicación a terceros. De los infractores se exigirá el correspondiente resarcimiento de daños y perjuicios. Se reserva todos los derechos para el caso de la concesión de patente de invención o el registro de Modelo Industrial.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts ist nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten.

Copying of this document, and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.



- 1 FOR PLASTIC PARTS (POS. 1 AND 2):
 - LENGTHS: DIN 16901/130,
 - ANGLES, FORMS: DIN 7168-m, R,
 FOR METAL PARTS (POS. 3 AND 4): DIN 7168-m,
 FOR SCREWS (POS. 5 AND 6): DIN 7981 F-H.

P/N 9 contacts version: V42254-A6000-G*09

 TE Connectivity		Maßstab	
Datum: 30.08.88 Bearb: De Petter Gepr: PD Com P&SE Norm:		D-Sub housing shielded 9 contacts	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		V42254-A6000-G***-*-27	
customer drawing number: C 1393738-1		page 1+ of 6	

E	REVISÉ PER ECO-21-002428	22FEB21	AK
D	ECO-12-017358	22JAN13	CWR
C	ECO-12-008266	28AUG12	CWR
Zust	Mitteilung	Datum	Name









Con questa espresión autográfica queda formalmente prohibida la reproducción total o parcial de este documento, así como su uso indebido y/o su exhibición o comunicación a terceros. De los infractores se exigirá el correspondiente resarcimiento de daños y perjuicios. Se reserva todos los derechos para el caso de la concesión de patente de invención o el registro de Modelo Industrial.

Weitergabe sowie Verwertung dieses Unterlage, Verwertung und Mitteilung ihres Inhalts ist nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder G.M. Untertage vorbehalten.

Copying of this document and giving it to others and the use or communication of the contents thereof are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.

A
B
C
D
E
F

A
B
C
D



housing		dimension									
P/N	No. of contacts	A	B	C	D	E	F	G	H	J	K
V42254-A6000-											
G × 15	15					28	39,62		R3	14,5	R4,5
G × 25	25	13	14	1	7,5	41,8	53,52	6,5	R4	16	R5,5
G × 37	37					58,25	69,8				
G × 50	50	16	17,5	1,5	9,5	55,78	67,41	9,5	R5,5	20,6	R7

2) only for the 37 contacts version

1) tape only for the 15 to 37 contacts versions
drawn is the 25 contacts version

				Maßstab	
				TE TE Connectivity	
				D-Sub housing	
				shielded 15 to 50 contacts	
				V42254-A6000-G***-27	
				customer drawing number: C 1393738-1	
				page 2+	
				of 6	

V 4 2 2 5 4 - A 6 0 0 * - G * * *

Housing type

G plastic housing, shielded

Marking and colour of the housing

1 TE-marking, grey

2 without marking, grey


3 TE-marking, black

4 without marking, black

	wire diameter					No. of contacts - housing size	
	0	1	2	3	4		
Packaging	set 1)	4-8	6-8		4-8	09	9 contact - housing size 1
	200 2)	5-10	5-8		5-10	15	15 contacts - housing size 2
	200 2)	5-11	5-8,5		5-11	25	25 contacts - housing size 3
	200 2)	6-11	6-8	10-11	6-11	37	37 contacts - housing size 4
	200 2)	9-14,5	12-14,5		9-14,5	50	50 contacts - housing size 5
							1) per set, in blister - 9 and 15 contacts : 25 - 25, 37 and 50 contacts : 15 2) loose pieces, in cardboard : 200



TE Connectivity



LOC DIMENSIONS IN MM
GW

SCALE

WEIGHT

MATERIAL

NAME

D-Sub Housing

shielded

DWG NO.

V42254-A6000-G***-*-27

SHT. 3+

REV.	CHANGE ORDER	DATE	APP.	customer drawing number: C 1393738-1	OF 6
------	--------------	------	------	--------------------------------------	------

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

PROPRIETARY:

1	2	3	4																																																																		
A	Active part numbers. Contact Tyco Electronics for other configuration availability <table border="1" style="width:100%; border-collapse: collapse;"> <thead> <tr> <th style="width:50%;">Old Part Number</th> <th style="width:50%;">TE Part Number</th> </tr> </thead> <tbody> <tr><td>V42254-A6000-G109</td><td>1393738-1</td></tr> <tr><td>V42254-A6000-G115</td><td>1393738-2</td></tr> <tr><td>V42254-A6000-G125</td><td>1393738-3</td></tr> <tr><td>V42254-A6000-G137</td><td>1393738-4</td></tr> <tr><td>V42254-A6000-G150</td><td>1393738-5</td></tr> <tr><td>V42254-A6000-G209</td><td>1393738-6 OBSOLETE</td></tr> <tr><td>V42254-A6000-G309</td><td>1393738-7 OBSOLETE</td></tr> <tr><td>V42254-A6000-G315</td><td>1393738-8 OBSOLETE</td></tr> <tr><td>V42254-A6000-G325</td><td>1393738-9 SUPERSEDED BY 1393738-1</td></tr> <tr><td>V42254-A6001-G109</td><td>4-1393738-2 OBSOLETE</td></tr> <tr><td>V42254-A6001-G125</td><td>4-1393738-4 SUPERSEDED BY 6-1393738-1</td></tr> <tr><td>V42254-A6001-G309</td><td>4-1393738-5 SUPERSEDED BY 1-1393739-9</td></tr> <tr><td>V42254-A6001-G315</td><td>4-1393738-6 SUPERSEDED BY 6-1393738-7</td></tr> <tr><td>V42254-A6002-G109</td><td>5-1393738-0 OBSOLETE</td></tr> <tr><td>V42254-A6002-G125</td><td>5-1393738-2 SUPERSEDED BY 6-1393738-1</td></tr> <tr><td>V42254-A6003-G137</td><td>5-1393738-7 SUPERSEDED BY 6-1393738-2</td></tr> <tr><td>V42254-A6004-G109</td><td>5-1393738-9</td></tr> <tr><td>V42254-A6004-G115</td><td>6-1393738-0</td></tr> <tr><td>V42254-A6004-G125</td><td>6-1393738-1</td></tr> <tr><td>V42254-A6004-G137</td><td>6-1393738-2</td></tr> <tr><td>V42254-A6004-G150</td><td>6-1393738-3</td></tr> <tr><td>V42254-A6004-G209</td><td>6-1393738-4 SUPERSEDED BY 5-1393738-9</td></tr> <tr><td>V42254-A6004-G215</td><td>6-1393738-5 OBSOLETE</td></tr> <tr><td>V42254-A6004-G225</td><td>6-1393738-6 OBSOLETE</td></tr> <tr><td>V42254-A6004-G309</td><td>1-1393739-9 OBSOLETE</td></tr> <tr><td>V42254-A6004-G315</td><td>6-1393738-7 OBSOLETE</td></tr> <tr><td>V42254-A6004-G325</td><td>2-1393739-0 OBSOLETE</td></tr> <tr><td>V42254-A6004-G337</td><td>2-1393739-1 SUPERSEDED BY 6-1393738-2</td></tr> <tr><td>V42254-A6004-G350</td><td>2-1393739-2 SUPERSEDED BY 6-1393738-3</td></tr> <tr><td>V42254-A6004-G409</td><td>6-1393738-8 OBSOLETE</td></tr> <tr><td>V42254-A6004-G415</td><td>6-1393738-9 OBSOLETE</td></tr> <tr><td>V42254-A6004-G437</td><td>7-1393738-1 OBSOLETE</td></tr> </tbody> </table>			Old Part Number	TE Part Number	V42254-A6000-G109	1393738-1	V42254-A6000-G115	1393738-2	V42254-A6000-G125	1393738-3	V42254-A6000-G137	1393738-4	V42254-A6000-G150	1393738-5	V42254-A6000-G209	1393738-6 OBSOLETE	V42254-A6000-G309	1393738-7 OBSOLETE	V42254-A6000-G315	1393738-8 OBSOLETE	V42254-A6000-G325	1393738-9 SUPERSEDED BY 1393738-1	V42254-A6001-G109	4-1393738-2 OBSOLETE	V42254-A6001-G125	4-1393738-4 SUPERSEDED BY 6-1393738-1	V42254-A6001-G309	4-1393738-5 SUPERSEDED BY 1-1393739-9	V42254-A6001-G315	4-1393738-6 SUPERSEDED BY 6-1393738-7	V42254-A6002-G109	5-1393738-0 OBSOLETE	V42254-A6002-G125	5-1393738-2 SUPERSEDED BY 6-1393738-1	V42254-A6003-G137	5-1393738-7 SUPERSEDED BY 6-1393738-2	V42254-A6004-G109	5-1393738-9	V42254-A6004-G115	6-1393738-0	V42254-A6004-G125	6-1393738-1	V42254-A6004-G137	6-1393738-2	V42254-A6004-G150	6-1393738-3	V42254-A6004-G209	6-1393738-4 SUPERSEDED BY 5-1393738-9	V42254-A6004-G215	6-1393738-5 OBSOLETE	V42254-A6004-G225	6-1393738-6 OBSOLETE	V42254-A6004-G309	1-1393739-9 OBSOLETE	V42254-A6004-G315	6-1393738-7 OBSOLETE	V42254-A6004-G325	2-1393739-0 OBSOLETE	V42254-A6004-G337	2-1393739-1 SUPERSEDED BY 6-1393738-2	V42254-A6004-G350	2-1393739-2 SUPERSEDED BY 6-1393738-3	V42254-A6004-G409	6-1393738-8 OBSOLETE	V42254-A6004-G415	6-1393738-9 OBSOLETE	V42254-A6004-G437	7-1393738-1 OBSOLETE
Old Part Number	TE Part Number																																																																				
V42254-A6000-G109	1393738-1																																																																				
V42254-A6000-G115	1393738-2																																																																				
V42254-A6000-G125	1393738-3																																																																				
V42254-A6000-G137	1393738-4																																																																				
V42254-A6000-G150	1393738-5																																																																				
V42254-A6000-G209	1393738-6 OBSOLETE																																																																				
V42254-A6000-G309	1393738-7 OBSOLETE																																																																				
V42254-A6000-G315	1393738-8 OBSOLETE																																																																				
V42254-A6000-G325	1393738-9 SUPERSEDED BY 1393738-1																																																																				
V42254-A6001-G109	4-1393738-2 OBSOLETE																																																																				
V42254-A6001-G125	4-1393738-4 SUPERSEDED BY 6-1393738-1																																																																				
V42254-A6001-G309	4-1393738-5 SUPERSEDED BY 1-1393739-9																																																																				
V42254-A6001-G315	4-1393738-6 SUPERSEDED BY 6-1393738-7																																																																				
V42254-A6002-G109	5-1393738-0 OBSOLETE																																																																				
V42254-A6002-G125	5-1393738-2 SUPERSEDED BY 6-1393738-1																																																																				
V42254-A6003-G137	5-1393738-7 SUPERSEDED BY 6-1393738-2																																																																				
V42254-A6004-G109	5-1393738-9																																																																				
V42254-A6004-G115	6-1393738-0																																																																				
V42254-A6004-G125	6-1393738-1																																																																				
V42254-A6004-G137	6-1393738-2																																																																				
V42254-A6004-G150	6-1393738-3																																																																				
V42254-A6004-G209	6-1393738-4 SUPERSEDED BY 5-1393738-9																																																																				
V42254-A6004-G215	6-1393738-5 OBSOLETE																																																																				
V42254-A6004-G225	6-1393738-6 OBSOLETE																																																																				
V42254-A6004-G309	1-1393739-9 OBSOLETE																																																																				
V42254-A6004-G315	6-1393738-7 OBSOLETE																																																																				
V42254-A6004-G325	2-1393739-0 OBSOLETE																																																																				
V42254-A6004-G337	2-1393739-1 SUPERSEDED BY 6-1393738-2																																																																				
V42254-A6004-G350	2-1393739-2 SUPERSEDED BY 6-1393738-3																																																																				
V42254-A6004-G409	6-1393738-8 OBSOLETE																																																																				
V42254-A6004-G415	6-1393738-9 OBSOLETE																																																																				
V42254-A6004-G437	7-1393738-1 OBSOLETE																																																																				
B																																																																					
C																																																																					
D																																																																					
E																																																																					
F	LOC GW DIMENSIONS IN MM <table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">SCALE</td> <td style="width: 50%;">WEIGHT</td> </tr> <tr> <td colspan="2">MATERIAL</td> </tr> <tr> <td colspan="2">NAME</td> </tr> <tr> <td colspan="2">D-Sub Housing</td> </tr> <tr> <td colspan="2">shielded</td> </tr> <tr> <td>DWG NO.</td> <td>SHT. 4+</td> </tr> <tr> <td colspan="2">V42254-A6000-G***-*-27</td> </tr> </table> <table border="1" style="width:100%; border-collapse: collapse; margin-top: 10px;"> <tr> <td style="width: 10%;">REV.</td> <td style="width: 20%;">CHANGE ORDER</td> <td style="width: 10%;">DATE</td> <td style="width: 10%;">APP.</td> <td style="width: 50%;">Customer Drawing: C 1393738-1</td> <td style="width: 10%;">OF 6</td> </tr> </table>			SCALE	WEIGHT	MATERIAL		NAME		D-Sub Housing		shielded		DWG NO.	SHT. 4+	V42254-A6000-G***-*-27		REV.	CHANGE ORDER	DATE	APP.	Customer Drawing: C 1393738-1	OF 6																																														
SCALE	WEIGHT																																																																				
MATERIAL																																																																					
NAME																																																																					
D-Sub Housing																																																																					
shielded																																																																					
DWG NO.	SHT. 4+																																																																				
V42254-A6000-G***-*-27																																																																					
REV.	CHANGE ORDER	DATE	APP.	Customer Drawing: C 1393738-1	OF 6																																																																

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.


PROPRIETARY:

V 4 2 2 5 4 - A 6 1 * * - L 1

Technical data		
	contact tube outer diameter ±0.1	for shield braiding outer diameter
04	4	2.0 to 2.7
05	5	2.8 to 3.7
06	6	3.8 to 4.7
07	7	4.8 to 5.7
08	8	5.8 to 6.7
09	9	6.8 to 7.7
10	10	7.8 to 8.7
11	11	8.8 to 9.7
12	12	9.8 to 10.7
13	13	10.8 to 11.7
14	14	11.8 to 12.7
15	15	12.8 to 13.7

Active part numbers. Contact
Tyco Electronics for
other configuration availability

Old Part Number	TE Part Number	
V42254-A6104-L1	3-1393561-2	OBSOLETE
V42254-A6105-L1	3-1393561-3	
V42254-A6106-L1	3-1393561-4	
V42254-A6107-L1	3-1393561-5	
V42254-A6108-L1	3-1393561-6	
V42254-A6109-L1	3-1393561-9	
V42254-A6110-L1	4-1393561-0	
V42254-A6111-L1	4-1393561-1	OBSOLETE
V42254-A6112-L1	4-1393561-2	
V42254-A6113-L1	4-1393561-3	OBSOLETE
V42254-A6114-L1	4-1393561-4	OBSOLETE
V42254-A6115-L1	5-1393502-9	OBSOLETE

APPLICABLE SPEC.:				FINISH					
 TE Connectivity				 DIMENSIONS IN MM		DIMENSIONS APPLY		PLATING	
						SCALE		WEIGHT	
LOC GW				DATE 30.08.88 NAME De Petter DEP. PD Com P&SE EC		MATERIAL			
						NAME D-Sub Housing			
E SEE SHEET 1 D SEE SHEET 1				TOLERANCE UNLESS SPECIFIED OTHERWISE		accessories: contact tubes			
						DWG NO. V42254-A6000-G***-*-27			
REV. CHANGE ORDER		DATE		APP.		customer drawing number: C 1393738-1			
						SHT. 5+ OF 6			

V 4 2 2 5 4 - A 6 2 * * - L * * *

Technical Data			
		bushing inner diameter ±0.2	cable outer diameter
00	1) 2)	/	/
05	3)	5	4.2 to 4.9
06	3)	6	5.0 to 5.9
07	3)	7	6.0 to 6.9
08	3)	8	7.0 to 7.9
09	3)	9	8.0 to 8.9
10	2)	10	9.0 to 9.9
11	2)	11	10.0 to 10.9
12	4)	12	11.0 to 11.9
13	4)	13	12.0 to 12.9
14	4)	14	13.0 to 13.9
15	4)	15	14.0 to 14.9

	contacts	colour
1	9 to 37	grey
50	50	grey
100	9 to 37	black
150	50	black

Active part numbers. Contact Tyco Electronics for other configuration availability

Old Part Number	TE Part Number	
V42254-A6200-L 1	4-1393561-5	OBSOLETE
V42254-A6200-L 50	4-1393561-6	
V42254-A6200-L100	5-1393502-1	OBSOLETE
V42254-A6200-L150	5-1393502-2	OBSOLETE
V42254-A6205-L 1	4-1393561-7	
V42254-A6205-L100	4-1393561-8	
V42254-A6206-L 1	4-1393561-9	
V42254-A6206-L100	5-1393561-0	
V42254-A6207-L 1	5-1393561-1	
V42254-A6207-L100	5-1393561-4	OBSOLETE
V42254-A6208-L 1	5-1393561-5	
V42254-A6208-L100	5-1393561-6	OBSOLETE
V42254-A6209-L 1	5-1393561-7	
V42254-A6209-L100	5-1393561-8	
V42254-A6210-L 1	5-1393561-9	
V42254-A6210-L 50	6-1393561-0	OBSOLETE
V42254-A6210-L100	6-1393561-1	OBSOLETE
V42254-A6210-L150	5-1393502-3	OBSOLETE
V42254-A6211-L 1	6-1393561-2	OBSOLETE
V42254-A6211-L 50	6-1393561-3	OBSOLETE
V42254-A6211-L100	5-1393502-4	OBSOLETE
V42254-A6211-L150	5-1393502-5	OBSOLETE
V42254-A6212-L 50	6-1393561-4	OBSOLETE
V42254-A6212-L150	5-1393502-6	OBSOLETE
V42254-A6213-L 50	6-1393561-5	OBSOLETE
V42254-A6213-L150	5-1393502-7	OBSOLETE
V42254-A6214-L 50	6-1393561-6	OBSOLETE
V42254-A6214-L150	5-1393502-8	OBSOLETE
V42254-A6215-L 50	8-1393501-5	OBSOLETE
V42254-A6215-L150	6-1393561-7	OBSOLETE

- 4) only for 50 contacts
3) only for 9 to 37 contacts
2) for 9 to 50 contacts
1) Blank bushing

APPLICABLE SPEC.				FINISH			
 TE Connectivity				DIMENSIONS APPLY		PLATING	
				SCALE		WEIGHT	
 DIMENSIONS IN MM				MATERIAL			
DATE 30.08.88 NAME De Petter DEP. PD Com P&SE EC				NAME			
TOLERANCE UNLESS SPECIFIED OTHERWISE				D-Sub Housing			
accessories: cable bushings				DWG NO.			
V42254-A6000-G****-27				SHT. 6			
REV. CHANGE ORDER				OF 6			
DATE APP. customer drawing number: C 1393738-1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1393561-9](#)