

D

C

B




A

D

C

B


A



- 1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 KAPTON VACUUM PICK UP BUTTON.
- 4 PLATING: CONTACTS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 5 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 6 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	33.00	37.43	40.00	12	3-1445052-2
OBSOLETE	30.00	34.43	37.00	11	3-1445052-1
OBSOLETE	27.00	31.43	34.00	10	3-1445052-0
OBSOLETE	24.00	28.43	31.00	9	2-1445052-9
OBSOLETE	21.00	25.43	28.00	8	2-1445052-8
	18.00	22.43	25.00	7	2-1445052-7
	15.00	19.43	22.00	6	2-1445052-6
	12.00	16.43	19.00	5	2-1445052-5
	9.00	13.43	16.00	4	2-1445052-4
	6.00	10.43	13.00	3	2-1445052-3
	3.00	7.43	10.00	2	2-1445052-2
	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 07OCT2000	 TE Connectivity		
DIMENSIONS: mm		CHK K. WHITAKER 20-FEB-2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 20-FEB-2001	NAME VERTICAL SURFACE MOUNT HEADER ASSY TIN CONTACTS, W/THRU HOLE HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™		
0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000 WEIGHT -			
MATERIAL 1		4	SIZE A2	CAGE CODE 00779	DRAWING NO. C-1445052
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV C5



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1445052-3](#)