





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C6	REVISED PER ECN-23-242776	15DEC2023	WLS	VS
	C7	REVISED PER ECN-24-256662	15MAR2024	WLS	VS



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 0.76µm MINIMUM GOLD ON MATING END,
2.54µm MINIMUM MATTE TIN ON SOLDER TAILS,
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.
- 6 PACKAGE REVERSE TAPED.

OBSOLETE	-9.00	16.27	16.00	4	6 6-1445100-4
OBSOLETE	-33.00	40.27	40.00	12	3-1445100-2
OBSOLETE	-30.00	37.27	37.00	11	3-1445100-1
	27.00	34.27	34.00	10	3-1445100-0
OBSOLETE	-24.00	31.27	31.00	9	2-1445100-9
	21.00	28.27	28.00	8	2-1445100-8
OBSOLETE	-18.00	25.27	25.00	7	2-1445100-7
	15.00	22.27	22.00	6	2-1445100-6
	12.00	19.27	19.00	5	2-1445100-5
	9.00	16.27	16.00	4	2-1445100-4
	6.00	13.27	13.00	3	2-1445100-3
	3.00	10.27	10.00	2	2-1445100-2
	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000		 TE Connectivity	
		CHK K. WHITAKER 17-APR-2001			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RIGHT ANGLE SURFACE MNT HEADER ASSY, 0.76 MIC GOLD CONTACTS, W/SURF MOUNT HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±° MATERIAL FINISH			
		PRODUCT SPEC 108-1836		SIZE A2	
		APPLICATION SPEC 114-13000		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C=1445100	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 OF 2	
				REV C7	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1445100-7](#)