



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-18-008642	05JUN2018	TD	TD
	A1	ECN-21-101658	30MAR2021	GTG	PK





SCALE 1:1 NOTES:

1. NO DAMAGE, SINK MARKS, CAVITIES OR FLOW LINES PERMITTED.
- 2 MATERIAL:
SEAL: 30 DUROMETER INHERENTLY LUBRICATED SILICONE
HOUSING: PA66 35% GF
- 3 MATERIAL:
SEAL: 30 DUROMETER INHERENTLY LUBRICATED SILICONE HIGHER TEAR STRENGTH.
HOUSING: PA66 35% GF
- 4 THIS AREA MUST BE KEPT FREE OF SCRATCHES,BURRS,AND OTHER DEFECTS.
- 5 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
- 6 THIS PART HAS NOT COMPLETED VALIDATION TESTING.



SECTION B - B



6	3	GREY	DARK BLUE	9.60	10.20	10.50	SIZE D	I-2840876-4
	2	YELLOW	DARK BLUE	9.60	10.20	10.50	SIZE D	2840876-4
5	3	RED	BLACK	9.00	9.60	9.90	SIZE C	I-2840876-3
5	2	BLUE	BLACK	9.00	9.60	9.90	SIZE C	2840876-3
	3	PURPLE	ORANGE	8.00	8.60	8.90	SIZE B	I-2840876-2
	2	RUST RED	ORANGE	8.00	8.60	8.90	SIZE B	2840876-2
	3	LT. BLUE	DARK GREY	5.40	6.10	6.30	SIZE A	I-2840876-1
	2	GREEN	DARK GREY	5.40	6.10	6.30	SIZE A	2840876-1
		SEAL COLOR	PLASTIC COLOR	MIN	MAX	E	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T. DEWITTE 05SEP2017
CHK T. DEWITTE 05SEP2017
APVD T. DEWITTE 05SEP2017



CABLE SEAL, OVERMOLDED, PCON12

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.15 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2°
MATERIAL 2 3	FINISH -

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

SIZE A3	CAGE CODE -	DRAWING NO C-2840876	RESTRICTED TO
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1 REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2840876-4](#)