







D
C
B
A



- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
 2. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
 3. MATERIAL: BLACK POLYSTYRENE.
 4. PACKING LENGTH PER 22" REEL: 63.0 m.
 5. COMPONENT LOAD PER 13" REEL: 1000.
 6. ANGLE TOLERANCE: $\pm 1^\circ$
 7. CARRIER CAMBER IS WITHIN 1 mm IN 250 mm.

W	32.00 ± 0.30	P	20.00 ± 0.10	A0	15.80 ± 0.10	B0	23.30 $^{+0.15}_{-0.05}$
S	28.40 ± 0.10	P0	4.00 ± 0.10	A1	12.50 ± 0.10	B1	21.50 ± 0.10
E	1.75 ± 0.10	P2	2.00 ± 0.10	A2		B2	
F	14.20 ± 0.15	D0	$\varnothing 1.50^{+0.10}_{-0.00}$	K0	3.30 ± 0.10	K2	0.70 ± 0.10
T	0.35 ± 0.05	D1		K1	2.70 ± 0.10	COLOR: BK/ANT	

SIZE	DWG. NO.	REV
B	BAT-HLD-002-SMT-TR	B
SCALE: 4:1	DO NOT SCALE DRAWING	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[BAT-HLD-002-SMT](#)