







D
C
B
A



- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
 2. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
 3. MATERIAL: BLACK POLYSTYRENE.
 4. PACKING LENGTH PER 22" REEL: 63.0 m.
 5. COMPONENT LOAD PER 13" REEL: 1000.
 6. ANGLE TOLERANCE: $\pm 1^\circ$
 7. CARRIER CAMBER IS WITHIN 1 mm IN 250 mm.

W	32.00±0.30	P	20.00±0.10	A0	15.80±0.10	B0	23.30 ^{+0.15} _{-0.05}
S	28.40±0.10	P0	4.00±0.10	A1	12.50±0.10	B1	21.50±0.10
E	1.75±0.10	P2	2.00±0.10	A2		B2	
F	14.20±0.15	D0	Ø1.50 ^{+0.10} _{-0.00}	K0	3.30±0.10	K2	0.70±0.10
T	0.35±0.05	D1		K1	2.70±0.10	COLOR: BK/ANT	

SIZE	DWG. NO.	REV
B	BAT-HLD-002-SMT-TR	B
SCALE: 4:1	DO NOT SCALE DRAWING	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[BAT-HLD-002-SMT-TR](#)