





- NOTES: (UNLESS OTHERWISE SPECIFIED)
- 1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
  - 2. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE  $\pm 0.2\text{MM}$ .
  - 3. MATERIAL: BLACK POLYSTYRENE.
  - 4. PACKING LENGTH PER 22" REEL: 33.0 m.
  - 5. COMPONENT LOAD PER 13" REEL: 500.
  - 6. ANGLE TOLERANCE:  $\pm 1^\circ$
  - 7. CARRIER CAMBER IS WITHIN 1 mm IN 250 mm.

W	32.00±0.30	P	20.00±0.10	A0	15.20±0.10	B0	21.90±0.10
S	28.40±0.10	P0	4.00±0.10	A1	12.50 <sup>+0.15</sup> <sub>-0.05</sub>	B1	21.50±0.10
E	1.75±0.10	P2	2.00±0.10	A2		B2	
F	14.20±0.15	D0	Ø1.50 <sup>+0.10</sup> <sub>-0.00</sub>	K0	6.70±0.10	K2	0.70±0.10
T	0.40±0.05	D1		K1	2.70±0.10	COLOR: BK/ANT	

SIZE	DWG. NO.	REV
<b>B</b>	BAT-HLD-002-THM-TR	<b>B</b>
SCALE: 3:1	DO NOT SCALE DRAWING	SHEET 2 OF 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[BAT-HLD-002-THM](#)