




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER PCN-21-118564	04MAR2022	DRK	CB



D



C



B



DRC26-60S01



DRC26-60S02



DRC26-60S03




DRC26-60S04




DRC26-60S05




DRC26-60S06




DRC26-60S07




DRC26-60S08



DRC26-60S09



DRC26-60S10



KEY ORIENTATION

TCPN	ALIAS PART NUMBER
DRC26-60S01	DRC26-60S01
DRC26-60S02	DRC26-60S02
DRC26-60S03	DRC26-60S03
DRC26-60S04	DRC26-60S04
DRC26-60S05	DRC26-60S05
DRC26-60S06	DRC26-60S06
DRC26-60S07	DRC26-60S07
DRC26-60S08	DRC26-60S08
DRC26-60S09	DRC26-60S09
DRC26-60S10	DRC26-60S10

5. MATERIAL: HOUSING: PA46 30% GF (BLACK); BOLT: STEEL, TRIVALENT ZINC PLATED (ROHS COMPLIANT); CLIP: STEEL; GROMMET: VMQ

4. THIS PLUG MATES WITH 0944328L**-**** RECPTACLE. (** = KEY ARRANGEMENT; **** = ALL MODIFICATIONS)

3. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

2. RECOMMENDED RETAINING BOLT TORQUE: 25-28 IN-LB [2.82-3.16Nm]

1. PLUG IS SUPPLIED WITH DUST CAP. (NOT SHOWN)

NOTES:

CONTACT SIZE	MIN. O.D.	MAX. O.D.	WIRE GAUGE RANGE
20	.040 [1.016]	.095 [2.413]	16 - 20 [1.00-0.50mm ²]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D MEYER 10SEPT999	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK B BYFORD 20JUN2008		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.025 [.64] 4 PLC ±- ANGLES ±- FINISH - -	APVD D MEYER 20JUN2008	NAME PLUG 60 CONTACTS, SIZE 20 DRC SERIES	
		PRODUCT SPEC 108-151052	SIZE A2	
MATERIAL 5		APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C=DRC26-60SXX
CUSTOMER DRAWING			SCALE 3:2	SHEET 1 OF 1
			REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DRC26-60S04](#)