


BUCHANAN WireMate TWO-PIECE POKE-IN SERIES

TE Connectivity's (TE) BUCHANAN WireMate two-piece poke-in series of products provide designers a three directional solution for wall mounting a device and improve the overall installation experience for the novice installer. Wires are routed through an opening in the wall to TE's BUCHANAN WireMate connector mounted on a wall plate. The wires are stripped of insulation and easily poked into the terminal block device providing a reliable termination without the need for tooling. Wire extracting is also made easy, with simple levers to release individual wires. The mating header is surface mount attached to the PCB in the device to be mounted on the wall. The two-piece combination allows wall mounting of a device in three different directions; into the wall, along the wall and in a twist or rotating motion.



Applications

- Thermostats
- Smoke detectors
- Control panels
- Environmental monitors

Electrical

- **Current Rating:** 5A (18 AWG); 3A (20-24 AWG)
- **Voltage Rating:** 250 VAC

Mechanical

- 2mm panel thickness
- 18-24 AWG (solid); 18-22 AWG (stranded*)
- 10mm height (from wall plate to PCB)

Specifications

- **Product specification:** [108-133105](#)
- **Application specification:** [114-133111](#) (header)
[114-133105](#) (connector)
- UL E60677

Materials

- **Header:** LCP (UL-94 V0)
- **Connector housing:** PBT
- **Contact:** Cu-alloy, Sn plated
- **Operating temperature:** -40 to 85°C

*Submitted to UL


Benefits

- Installation time-saving with poke-in termination verses screw style termination
- Simple lever design for release of one wire at a time
- Provides flat connector surface reserved for wire marking (color options available)
- Allows easy wiring for home installation with tool-less poke-in wire termination
- Achieve a clear point of entry for wire insertion
- Improve installation experience with three mating directions

Product Selection Information



5mm Connector

mates with **5mm Header**

Positions	Connector PN's	Description	Positions	Header PN's	Description
2	2319461-2	BUCHANAN WireMate Two-Piece Poke-In Connector  2319461-3	2	2318770-2	BUCHANAN WireMate Two-Piece Poke-In Header  2318770-3
3	2319461-3		3	2318770-3	
4	2319461-4		4	2318770-4	
5	2319461-5		5	2318770-5	
6	2319461-6		6	2318770-6	
7	2319461-7		7	2318770-7	
8	2319461-8		8	2318770-8	

8mm Connector

mates with **8mm Header**

Positions	Plug PN's	Description	Positions	Header PN's	Description
2	2318582-2	BUCHANAN WireMate Two-Piece Poke-In Connector  2318582-5	2	2318136-2	BUCHANAN WireMate Two-Piece Poke-In Header  2318136-5
3	2318582-3		3	2318136-3	
4	2318582-4		4	2318136-4	
5	2318582-5		5	2318136-5	
6	2318582-6		6	2318136-6	
7	2318582-7		7	2318136-7	
8	2318582-8		8	2318136-8	

te.com

© 2018 TE Connectivity. All Rights Reserved. BUCHANAN, TE, TE Connectivity, and the TE connectivity (logo) are trademarks of TE Connectivity. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-773929-6 JN 08/2018

USA: +1 (800) 522-6752
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America: +54 (0) 11-4733-2200
 Germany: +49 (0) 6251-133-1999
 UK: +44 (0) 800-267666
 France: +33 (0) 1-3420-8686
 The Netherlands: +31 (0) 73-6246-999
 China: +86 (0) 400-820-6015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2318582-5](#)