










Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
Verpackungseinheit: 900 Stück
packaging unit: 900 pcs




Abspulrichtung - Reel off direction



Sperrfläche für Leiterbahnen gültig bei Verwendung von
Gegenstecker Federleiste 90° in IDC Ausführung
Restricted area for conductors valid for use by mating
female connector 90° in IDC version

Layoutvorschlag
recommended layout



Kontaktbezeichnung bei Pin 1
contact marking at pin 1

Anforderungsstufe 1
performance level 1


Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinnt 4-6 µm
terminal area 4-6 µm tin plating

Koplanarität der Anschlüsse ≤ 0,1 mm
coplanarity area of termination ≤ 0.1 mm

504258		rot red	1,5	
504257		grün green	1,5	
504256		blau blue	0,5	
504255		schwarz black	0,5	
Ident-Nr. part-no.	Codierung coding	Farbe colour	A	Bemerkung remark

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 9001 to be observed.

Information:				Tolerances ISO 2768-FH ISO 8015		 All Dimensions in mm		Scale 5:1					
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation M 1.27 MCB-A SMT 04-pin					
c		31.07.2018				www.ERNI.com		504254				I	
Index		Date						Class				MCBA	A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[504255](#) [504255-E](#)