





- bestückt / *assemble*



1) $\varnothing 1,0 \pm 0,09$ Durchmesser des metallisierten Loches
 $\varnothing 1,0 \pm 0,06$ *Diameter of finished plated-through hole*
 $\varnothing 1,15 \pm 0,025$ Bohrungsdurchmesser des Loches
 $\varnothing 1,15 \pm 0,025$ *Diameter of drilled hole*

Consider protection memo from DIN 34	Information:			Tolerances			Scale	2:1	
	All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		All Dimensions in mm	Designation Federleiste CD 128 EE <i>Fem. Connector CD 128 Pressfit</i>		
					www.ERNI.com		284181		
Index								STVCD	
						N:00062253.SZA			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284181](#)