





REV. 0

DCO 170439

COIL: @ 25°C
 RESISTANCE 552 OHMS ±10%
 NOMINAL VOLTAGE 20.0 - 29.5 VDC
 MUST OPERATE 13.5 VDC
 MUST RELEASE 7.0 VDC MAX., 1.5 VDC MIN.


ENVIRONMENT:

VIBRATION 55 CPS TO 2000 CPS @ 15 g's
 SHOCK 50 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX.
 RELEASE 5 MS MAX.

DIELECTRIC 1000 VAC, BOUNCE 2.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:
 2 AMPS @ 28 VDC, 100,000 OPERATIONS

DR. PBB 3/14/01

CKJLG 03-14-01

CII Technologies
 advanced control electronic solutions

CUST. CII STD.
 CUST. NO. REV.

3SAE RELAY

3SAE51B4K1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SAE5134K1](#)