

4

3

2

1




SPECIFICATIONS:

CONTACT RATING: 0.4 VA MAX @ 20 VDC OR PEAK AC.
INITIAL CONTACT RESISTANCE: 1,000 MEGOHMS MIN AT 500 VDC.
DIELECTRIC STRENGTH: 1,000 VOLTS RMS AT SEA LEVEL.
TERMINAL SEAL: EPOXY SEALED.
HARDWARE INCLUDED: (1) HEX NUT (1) LOCK WASHER.

SEAL - TOGGLE TO BUSHING:
SEAL TEST - SEAL SHALL WITHSTAND 3 FT OF WATER FOR 30 MINUTES.
DYNAMIC - TEST WHEN ACTIVATED 10 TIMES PER MINUTE FOR 10,000 CYCLES SEAL SHALL WITHSTAND A 2 INCH HEAD OF WATER.

NOTES:

- 1. CUSTOMER PART NUMBER CENTERED HERE.
- 2. INTERPRET DRAWING PER ASME Y14.5M-1994.



TTE-70973	2-1	NONE	2-3
MODEL NO.			
TERMINALS CONNECTED WHEN TOGGLE IS IN THE POSITIONS AS SHOWN.			
NOTE: TERMINAL DESIGNATION NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON SWITCH.			

AUGAT D/N TTE-70973

REV	B	REVISED 063C-0099-03 DATE: 10JUN03 APP'D: MZ	THIRD ANGLE PROJECTION	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DO NOT SCALE PRINT	ORIGINAL DATE OF DRAWING: 12-1-86		TYCO ELECTRONICS			
					FILE NAME: TTE70973	DIRECTORY: TOGSWTCH	DRAWN: B.L.	DATE: 12-1-86	TITLE: TTE SPECIAL CUSTOMER: MOTOROLA	
					MATERIAL: N/A		CHECKED: PAUL SMITH	DATE: 12-1-86		
					FINISH: N/A		APPROVED: T. SHEK	DATE: 12-4-86	DWG. NO. 1-1437563-7	REV. B
							CODE IDENT. NO. 91506		DWG. SIZE C	PRODUCT CODE: A51
				NEXT ASSY:		SCALE: 4:1	SHEET 1 OF 1			

4

3

2

CUSTOMER DRAWING

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TTE70973](#)