

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		C	0G3C-0588-03	14MAR07	BSV	MS

SPECIFICATIONS:


MATERIALS:  
CONTACTS: COPPER WITH GOLD PLATE OVER NICKEL PLATE.  
CASE: HIGH TEMPERATURE POLYESTER, 94V-0.  
SLIDER: POLYESTER.

ELECTRICAL:  
CONTACT RATING: 0.4 VA MAX. 20V MAX. (AC/DC).  
CONTACT RESISTANCE: 40m $\Omega$  MAX @ 100 mV/100 mA  
DIELECTRIC STRENGTH: 1000 VOLTS RMS @ SEA LEVEL.  
INSULATION RESISTANCE: 1000 MEGOHMS @ 500 VDC.  
LIFE: 60,000 - 80,000 CYCLES.








ENVIRONMENTAL:  
OPERATING TEMPERATURE: -20°C TO +80°C (-4°F TO +176°F).  
STORAGE: -20°C TO +80°C (-4°F TO +176°F).

NOTES:


- 1 EPOXY SEAL - 2-1437579-9 ONLY.
2. SOLDERABILITY PER EIA 364-52 CLASS 2 CATEGORY 1



TYCO PT. NO.	MODEL NO.	TYPE	POSN	ACTION
1-1437579-1	TSS11DG-RA	SPDT	2	ON-NONE-ON
1-1437579-5	TSS11EG-RA	SPDT	3	ON-OFF-ON
2-1437579-0	TSS21NG-RA	DPDT	2	ON-NONE-ON
2-1437579-4	TSS21PG-RA	DPDT	3	ON-OFF-ON
-	TSS21PAG-RA	DPDT	3	ON-ON-ON
2-1437579-9	TSS70932	SPDT	2	ON-NONE-ON



PC CUTOUT FOR SP



PC CUTOUT FOR DP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SWEENEY 13NOV1978	<b>tyco</b> Tyco Electronics Corporation Harrisburg, Pa 17105-3808			
DIMENSIONS: mm		CHK M SARVER 19APR04	NAME OUTLINE DRAWING TSS SLIDE SWITCH -			
		APVD M SARVER 19APR04				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE A2			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± -		APPLICATION SPEC				
MATERIAL SEE SPECIFICATIONS		WEIGHT -	CAGE CODE 00779	DRAWING NO C=1-1437579-1	RESTRICTED TO -	
FINISH SEE SPECIFICATIONS		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV C	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSS21NGRA](#)