

LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN
		C		0G3C-0588-03	14MAR07	BSV
					MS	

SPECIFICATIONS:


MATERIALS:
CONTACTS: COPPER WITH GOLD PLATE OVER NICKEL PLATE.
CASE: HIGH TEMPERATURE POLYESTER, 94V-0.
SLIDER: POLYESTER.

ELECTRICAL:
CONTACT RATING: 0.4 VA MAX. 20V MAX. (AC/DC).
CONTACT RESISTANCE: 40m Ω MAX @ 100 mV/100 mA
DIELECTRIC STRENGTH: 1000 VOLTS RMS @ SEA LEVEL.
INSULATION RESISTANCE: 1000 MEGOHMS @ 500 VDC.
LIFE: 60,000 - 80,000 CYCLES.


ENVIRONMENTAL:
OPERATING TEMPERATURE: -20°C TO +80°C (-4°F TO +176°F).
STORAGE: -20°C TO +80°C (-4°F TO +176°F).

NOTES:

1. EPOXY SEAL - 2-1437579-9 ONLY.
2. SOLDERABILITY PER EIA 364-52 CLASS 2 CATEGORY 1



TYCO PT. NO.	MODEL NO.	TYPE	POSN	ACTION
1-1437579-1	TSS11DG-RA	SPDT	2	ON-NONE-ON
1-1437579-5	TSS11EG-RA	SPDT	3	ON-OFF-ON
2-1437579-0	TSS21NG-RA	DPDT	2	ON-NONE-ON
2-1437579-4	TSS21PG-RA	DPDT	3	ON-OFF-ON
-	TSS21PAG-RA	DPDT	3	ON-ON-ON
2-1437579-9	TSS70932	SPDT	2	ON-NONE-ON



PC CUTOUT FOR SP

PC CUTOUT FOR DP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	R. SWEENEY	13NOV1978	tyco Electronics			Tyco Electronics Corporation Harrisburg, Pa 17105-3808					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	M SARVER	19APR04	NAME OUTLINE DRAWING TSS SLIDE SWITCH —						
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .010 4 PLC ± — ANGLES ± ±		APVD	M SARVER	19APR04							
				PRODUCT SPEC		—							
				APPLICATION SPEC		—							
MATERIAL		FINISH		WEIGHT	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
SEE SPECIFICATIONS		SEE SPECIFICATIONS				A2	00779	C-1-1437579-1		—			
CUSTOMER DRAWING						SCALE		4:1		SHEET	1 of 1	REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSS11DGRA](#)