

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	F	REVISION UPDATE TO F . NO CHANGE TO PARTS		13JUL2015	PS	JK

D—SUB CONNECTOR:

MATERIALS:

HOUSING: THERMOPLASTIC POLYESTER, 94V–0.
CONTACTS: COPPER ALLOY, GOLD PLATED.

MECHANICAL:

WIRE RANGE: 26–30 AWG SOLID, 28 AWG STRANDED.

TERMINAL BLOCK:

MATERIALS:

HOUSING: THERMOPLASTIC NYLON, BLACK, 94V–0.
TERMINALS: COPPER ALLOY, TIN PLATE.
SCREWS: 3M, BRASS, NICKEL PLATED.

ELECTRICAL CSA/UL:

RATING: 10A, 300V.

MECHANICAL:

WIRE RANGE: 14–22 AWG.



MOUNTING:

MATERIALS: RIGID PVC, GRAY.
MOUNTING: 2TK2 AND 2TK2D SERIES SNAPTRACK,
(SOLD SEPARATELY).


NOTES:

① CATALOG NUMBER MARKED HERE.

② CONTAINS NO TIN–LEAD PLATING.



②	2M25DSML	1776606–1
	2M25DSM	1–1437684–8
	CATALOG NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL	08JUL02	 TE Connectivity				
		CHK H. WAKEEM	7/8/02					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± .1 2 PLC ± .01 3 PLC ± – 4 PLC ± – ANGLES ± –	APVD H. WAKEEM	7/8/02	NAME 2M25DSM ASSEMBLY				
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		MATERIAL —	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1-1437684-8	RESTRICTED TO —
CUSTOMER DRAWING						SCALE NTS	SHEET 1 OF 1	REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776606-1](#)