

REVISIONS			
S/N	DESCRIPTION	DATE	APPROVED
K	0740-03 REDRAWN, ADDED ITEM 5	03/08/23	CC

CONSTRUCTION
NOMINAL VOLTAGE

HERMETICALLY SEALED
115 V, 400 HZ

CONTACT RATING

25 AMP AT 115 V, 400 HZ
10 AMP AT 28 VDC
15 AMP AT 115 V, 400 HZ




RES.
IND.

COIL RATING
PICKUP
DROPOUT

115V, 400 HZ
95 V MAX HOT
25 ±15V HOT

RATED DUTY
VIBRATION
MAX WEIGHT

CONTINUOUS
MIL-E-5272 PROC 1
7.5 OZ.



QTY	PART OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	FSM NO	DRAWING OR SPECIFICATION	MATERIAL OR NOTE
5	1	39529-001 OVERLAY - WIRING DIAGRAM			
4	1	20473-0501 CONTACTOR ASSEMBLY - PRIMARY			
3	1	19488-001 PLATE - WIRING DIAGRAM			
2	1	17959-001 PLATE - WARNING			
1	1	16043-001 PLATE - NAME			

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE	TERMINALS OR
2 PL. DEC. 13 PL. DEC. ANGLES	±1°
±.03	±.010

MATERIAL	DR BY	CSC	03/09/16
CHK BY	CC	03/09/18	
ENGR	CC	03/09/18	
MFG	JM	03/09/18	
SIZE	CODE IDENT		
C	74063		

SCALE	NONE	SHEET
DWG NO.	DHR-14B	
REF TYCO P/N	1-1616037-2	

tyco Electronics

14 Horton Blvd., 175 N. Diamond Street, Mansfield, Ohio 44922

CONTACTOR - 3PDT
HERMETICALLY SEALED 093

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DHR14B](#)