





LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J	REVISED PER ECO-15-008006	17NOV2015	NK	MM



- | | |
|---|--|
| 1 | NO. OF POSITIONS INDICATED PERTAINS TO THE HOUSING. |
| 2 | THIS COVER IS TO BE USED WITH 102536. |
| 3 | NO CENTER PART ON THIS PART. |
| 4 | OBSOLETE PART NUMBER. |
| 5 | MATERIAL: FLAME RETARDANT THERMOPLASTIC,
COLOR-BLACK. |

44.45[1.750]	96.42[3.796]	91.59[3.606]	88.90[3.500]	35	72	$\triangle_4$	-3	102537	-4-
43.18[1.700]	93.88[3.696]	89.05[3.506]	86.36[3.400]	34	70	$\triangle_4$	-3	102537	-3-
41.91[1.650]	91.34[3.596]	86.51[3.406]	83.82[3.300]	33	68	$\triangle_4$	-3	102537	-2-
40.64[1.600]	88.79[3.496]	83.97[3.306]	81.28[3.200]	32	66	$\triangle_4$	-3	102537	-1-
39.37[1.550]	86.26[3.396]	81.43[3.206]	78.74[3.100]	31	64		3-	102537	-0
38.10[1.500]	83.72[3.296]	78.89[3.106]	76.20[3.000]	30	62	$\triangle_4$	-2	102537	-9-
36.83[1.450]	81.18[3.196]	76.35[3.006]	73.66[2.900]	29	60		2-	102537	-8
35.56[1.400]	78.63[3.096]	78.81[2.906]	71.12[2.800]	28	58	$\triangle_4$	-2	102537	-7-
34.29[1.350]	76.09[2.996]	71.27[2.806]	68.58[2.700]	27	56	$\triangle_4$	-2	102537	-6-
33.02[1.300]	73.55[2.896]	68.73[2.706]	66.04[2.600]	26	54	$\triangle_4$	-2	102537	-5-
31.75[1.250]	71.01[2.796]	66.19[2.606]	63.50[2.500]	25	52	$\triangle_4$	-2	102537	-4-
30.48[1.200]	68.48[2.696]	63.65[2.506]	60.96[2.400]	24	50		2-	102537	-3
29.91[1.150]	65.94[2.596]	61.11[2.406]	58.42[2.300]	23	48	$\triangle_4$	-2	102537	-2-
27.94[1.100]	63.39[2.496]	58.57[2.306]	55.88[2.200]	22	46	$\triangle_4$	-2	102537	-1-
26.67[1.050]	60.85[2.396]	56.03[2.206]	53.34[2.100]	21	44	$\triangle_4$	-2	102537	-0-
25.40[1.000]	58.31[2.296]	53.49[2.106]	50.80[2.000]	20	42	$\triangle_4$	-1	102537	-9-
24.13[.950]	55.78[2.196]	50.95[2.006]	48.26[1.900]	19	40		1-	102537	-8
22.86[.900]	53.24[2.096]	48.41[1.906]	45.72[1.800]	18	38	$\triangle_4$	-1	102537	-7-
21.59[.850]	50.69[1.996]	45.87[1.806]	43.18[1.700]	17	36	$\triangle_4$	-1	102537	-6-
20.32[.800]	48.15[1.896]	43.33[1.706]	40.64[1.600]	16	34		1-	102537	-5
19.05[.750]	45.62[1.796]	40.79[1.606]	38.10[1.500]	15	32		1-	102537	-4
17.78[.700]	43.07[1.696]	38.25[1.506]	35.56[1.400]	14	30		1-	102537	-3
16.51[.650]	40.53[1.596]	35.71[1.406]	33.02[1.300]	13	28		1-	102537	-2
15.24[.600]	37.99[1.496]	33.17[1.306]	30.48[1.200]	12	26		1-	102537	-1
13.97[.550]	35.45[1.396]	30.63[1.206]	27.94[1.100]	11	24		1-	102537	-0
12.70[.500]	32.92[1.296]	28.09[1.106]	25.40[1.000]	10	22			102537	-9
11.43[.450]	30.38[1.196]	25.55[1.006]	22.86[.900]	9	20			102537	-8
10.16[.400]	27.84[1.096]	23.01[.906]	20.32[.800]	8	18			102537	-7
8.89[.350]	25.29[.996]	20.47[.806]	17.78[.700]	7	16			102537	-6
7.62[.300]	22.76[.896]	17.93[.706]	15.24[.600]	6	14			102537	-5
6.35[.250]	20.22[.796]	15.39[.606]	12.70[.500]	5	12			102537	-4
5.08[.200]	17.68[.696]	12.85[.506]	10.16[.400]	4	10			102537	-3
$\triangle_3$	15.14[.596]	10.31[.406]	7.62[.300]	3	8			102537	-2
$\triangle_3$	12.59[.496]	7.77[.306]	5.08[.200]	2	6			102537	-1

E	D	C	B	A	REF. 	PART NUMBER
COVER DIMENSIONS					NO OF POSN	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 06MAR09		 TE Connectivity	
		CHK JEFFREY GESFORD 06MAR09			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD JEFFREY GESFORD 06MAR09			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC -		COVER - HALF, LOW PROFILE MASS TERMINATION AMPMODU, .100CL, CENTER BAR POLARIZATION	
MATERIAL		APPLICATION SPEC -			
		FINISH -		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-102537	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV J	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102537-3](#)