




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL 130CTB7 CHK T. CLARK 200CTB7 APVD T. CLARK 200CTB7		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 □, VERTICAL, WITH .025 SQ POSTS	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE A2	
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POST: COPPER ALLOY		FINISH POST: .000015 GOLD ON CONTACT .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL ALL OVER .000050 NICKEL		CAGE CODE 00779	
		WEIGHT —		DRAWING NO C=103186	
CUSTOMER DRAWING				RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 of 1	
				REV 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103186-8](#)