



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	PART STATUS UPATED IN PART LIST TABLE	16FEB2018	SD	PS

D





C


B

A



- 1 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 3 SELECTIVE POSTS ARE FORMED TO PROVIDE CONNECTOR RETENTION TO PC BOARD UNTIL SOLDERED. RETENTION FEATURE IS FOR .055 MINIMUM PC BOARD THICKNESS.SEE DETAIL Z FOR FORM AND TABLE FOR LOCATIONS.
- 4 FINISH: POSTS: .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL ON ENTIRE POST.
- 5 FINISH: POSTS: .000100-.000200 MATTE TIN OVER .000050 NICKEL ON ENTIRE POST.
- 6 OBSOLETE



△6	△5	2,3,6,7	—	.795	.700	7	16	5-104421-1	
	△4	2,3,6,7	—	.795	.700	7	16	—104421-1	
PLATING		ROW N	ROW M	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	
		HOLD-DOWN POST CONFIG LOCATIONS							
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN SCOTT A. SHUEY 7-6-88	 TE Connectivity				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. FEIDT 10-6-88					
				APVO R. FEIDT 10-6-88	NAME HDR ASSY, MODU II, DR, .100 X .100 CL RT ANGLE, (1) SIDED SHROUD W/ HOLD DOWN —				
		PRODUCT SPEC							
		APPLICATION SPEC							
		—							
MATERIAL — HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR — BLACK		FINISH		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-104421	RESTRICTED TO —	
SEE TABLE				CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV H1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104421-1](#)