

4

THIS DRAWING IS UNPUBLISHED
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

3

RELEASED FOR PUBLICATION
FREI FUER VERÖFFENTLICHUNG

2

MATED WITH:
PASSEND ZU:

1

REVISIONS
ÄNDERUNGEN

LOC
A I

DIST
-

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	E4	TITLE BLOCK: NAME CHANGED	09OCT2015	ER	DO
	E5	NOTE 9 REVISED PER PCN E-15-016089	03NOV2015	ER	DO
	E6	PN 0-2: ITEM 3 ADDED PER PCN E-16-015832	09NOV2016	ER	DO
	E7	PN 0-5 ADDED PER PCN E-17-004754	03APR2017	ER	DO

© COPYRIGHT 2007

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN.

PROJEKT NR.:

71

25

56

close open

30

5

9

8

1

2

3

4

6

7

PN 0-1 AS SHOWN

-	-	-	-	2	SCREW FOR PLASTICS	STEEL	ZINC PLATED	WN5452, 8IP-2.5x8.0	9	
1	-	-	-	1	SCREEN TERMINATION	COPPER ALLOY	TIN PLATED	SERIES HC26, CONN.HSG	8	
-	-	-	1	1	RETAINING RING	BRASS	NICKEL PLATED	SERIES HC26, CONN./ COUPL. HSG.	7	
-	-	-	1	1	COUPLING NUT	PA66-GF25	GREY	SERIES HC26, CONN. HSG., DESIGN PLASTIC	6	
-	-	1	-	1	COVER	PA66-GF25	GREY	SERIES HC26, CONN. HSG., DESIGN PLASTIC	5	
-	-	-	1	1	ANGLED CONNECTOR HOUSING	PA66-GF25	GREY	SERIES HC26, DESIGN PLASTIC	4	
-	-	-	1	1	SEALING	FKM	GREY	SERIES HC26, WIRE SIZE 11.5-12.0	3	
-	-	-	1	1	SEALING	FKM	GREY	SERIES HC26, INTERMATE	2	
-	1	-	-	2	SCREW FOR PLASTICS	STEEL	ZINC PLATED	WN5452, 10IP-3.0x18.0	1	
0-5	0-4	0-3	0-2	0-1	DESCRIPTION	MATERIAL	SURFACE/COLOR	NOTE	ITEM	
QTY/PN					PARTS LIST (PER UNIT)					

DIMENSIONS:
MASSEINHEITEN:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES/WINKEL	±

MATERIAL

-

FINISH/OBERFLÄCHE/FARBE

-

DWN
H.BRAUN
25SEP2007

CHK
T.VETTER
27OCT2008

APVD
T.SCHNURPFIL
27OCT2008

PRODUCT SPEC
PRODUKTSPEZ.
108-74097

APPLICATION SPEC
VERARBEITUNGSSPEZ.
114-74103

WEIGHT
GEWICHT
-

Customer Drawing

/KUNDENZEICHNUNG

SCALE
MASSSTAB
1:1

SHEET
BLATT
1 OF
VON 1

REV
E7

TOLERANCING ISO 8015
TOLERIERUNG ISO 8015

TE Connectivity

NAME

ANGLED CONNECTOR HOUSING ASS'Y
SERIES HC26, DESIGN PLASTIC
CIRCULAR HYBRID CONNECTOR

SIZE

A3

CAGE CODE

00779

DRAWING NO
ZEICHNUNGS-NR.

C=1103434

RESTRICTED TO
NUR FUER

-

Notes

1

SUITABLE HOUSINGS: SERIES HC26
CUSTOMER DRAWING: 1103433, 1103470

2

SUITABLE INSERTS: SERIES HC26
CUSTOMER DRAWING: 1103428, 1103429, 1103431, 1103432

3

STANDARDS:
DIN EN 61984, DIN EN 60664-1

4

PACKAGING PN 0-1:
40 SETS IN A CARTON

5

PACKAGING PN 0-2:
500 PIECES IN A CARTON

6

PACKAGING PN 0-3:
500 PIECES IN A CARTON

7

PACKAGING PN 0-4:
1000 PIECES IN A CARTON

8

SUITABLE: ACCESSORY KIT:
CUSTOMER DRAWING 1103519

9

SEAL GLUED AROUND INTO ANGLED
CONNECTOR HOUSING WITH LOCTITE 406,
ACC. TO INSTRUCTION SHEET 408-18000

10

PACKAGING PN 0-5:
500 PIECES IN A CARTON

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[0-1103434-3](#)