

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		B3	REWORKED PER ECR 09-026789	08DEC2009	MH	BR
			B4	ECR-11-002636	05APR2011	SR	AR
			B5	REVISED PER ECR-16-016780	22AUG2017	NG	MKO



PN 1-1.2-1.3-1.4-1.5-1.1-2.2-2.3-2
4-2.5-2.6-1.4-3.1-8.2-8.3-8.4-8.5-8.
~~4-9.2-9.3-9.4-9~~ & ~~5-9~~



1	MATERIAL SEE TABLE
2	SURFACE SEE TABLE
3	ASSEMBLY WEIGHT SEE TABLE
4	PACKAGING: 50 PIECES IN POLY-BAG 0-1243085-8
5	PACKAGING: 500 PIECES IN POLY-BAG 0-1243085-8
6	PACKAGING: 10 PIECES IN POLY-BAG 0-1243085-8
7	CROSS-SECTION MARKING

[illegible][illegible]

HN.D-C-Bu.Ag.Au.1.5 mm 2
HN.D-C-Bu.Ag.Au.4.0 mm 2
HN.D-C-Bu.Cu.Ni.0.14 -0.37 mm 2
HN.D-C-Bu.Fe.Au.0.14 -0.37 mm 2
HN.D-C-Bu.Au.2.5 mm 2
HN.D-C-Bu.Au.1.5 mm 2
HN.D-C-Bu.Au.0.75-1.00 mm 2
HN.D-C-Bu.Au.0.5 mm 2
HN.D-C-Bu.Au.0.14 -0.37 mm 2
HN.D-C-Bu.Ag.2.5 mm 2
HN.D-C-Bu.Ag.1.5 mm 2
HN.D-C-Bu.Ag.0.75-1.00 mm 2
HN.D-C-Bu.Ag.0.5 mm 2
HN.D-C-Bu.Ag.0.14 -0.37 mm 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23.07.1997 Braun CHK 23.07.1997 Schnurppfeil		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768 mH-E DIN 9137-120		NAME SOCKET CONTACT SERIES HN.D	
		APVD - PRODUCT SPEC 108-74018 APPLICATION SPEC 114-74015		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL 		FINISH 		WEIGHT - A2 00779 C-1105051	
1 -		2 -		CUSTOMER DRAWING SCALE 10:1 SHEET 1 of 1 REV B5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1105051-8](#)