






LOC	DIST	REVISIONS				
		REV	DATE	BY	APP'D	
DF	FO	J	28APR11	CT	DH	
		J	TYCO LOGO REPLACED WITH THE AMP BRAND LOGO			



- 1 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 2 STANDOFFS: POSN 12 (9) STANDOFFS AS SHOWN.
POSN 16 (12) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 20 (15) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 24 (18) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 28 (21) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 32 (24) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 36 (27) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 40 (30) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 44 (33) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 48 (36) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 52 (39) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 56 (42) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 60 (45) STANDOFFS, 3 PER DIAGONAL ROW.
- 3 FINISH: BRIGHT TIN-LEAD .000100-.000200 THK OVER NICKEL .000050 MIN THK.
- 4 HEIGHT AFTER TERMINATION IS .238 REF.
- 5 CAVITY IDENTIFICATION MOLDED IN THIS AREA.
- 6 FINISH: BRIGHT TIN .000100-.000200 THK OVER NICKEL .000050 MIN THK.



	6	2.950	2.950	3.274	2.950	2.950	59	60	6-111035-3
	6	2.150	2.150	2.474	2.150	2.150	43	44	5-111035-9
	6	1.950	1.950	2.274	1.950	1.950	39	40	5-111035-8
	6	1.750	1.750	2.074	1.750	1.750	35	36	5-111035-7
	6	1.550	1.550	1.874	1.550	1.550	31	32	5-111035-6
	6	1.150	1.150	1.474	1.150	1.150	23	24	5-111035-4
	6	.950	.950	1.274	.950	.950	19	20	5-111035-3
	6	.750	.750	1.074	.750	.750	15	16	5-111035-2
	3	2.950	2.950	3.274	2.950	2.950	59	60	1-111035-3
OBSOLETE	3	2.750	2.750	3.074	2.750	2.750	55	56	1-111035-2
OBSOLETE	3	2.550	2.550	2.874	2.550	2.550	51	52	1-111035-1
OBSOLETE	3	2.350	2.350	2.674	2.350	2.350	47	48	1-111035-0
	3	2.150	2.150	2.474	2.150	2.150	43	44	111035-9
	3	1.950	1.950	2.274	1.950	1.950	39	40	111035-8
	3	1.750	1.750	2.074	1.750	1.750	35	36	111035-7
	3	1.550	1.550	1.874	1.550	1.550	31	32	111035-6
OBSOLETE	3	1.350	1.350	1.674	1.350	1.350	27	28	111035-5
	3	1.150	1.150	1.474	1.150	1.150	23	24	111035-4
	3	.950	.950	1.274	.950	.950	19	20	111035-3
	3	.750	.750	1.074	.750	.750	15	16	111035-2
OBSOLETE	3	.550	.550	.874	.550	.550	11	12	111035-1
	FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. PEACHEY 05-MAR-86
CHK M. SCULLY 23-MAY-86
APP'D D. HOFFMAN 23-MAY-86
NAME
PRODUCT SPEC
APPLICATION SPEC
114-40005
WEIGHT
CUSTOMER DRAWING

DIMENSIONS: INCHES

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

CONTACTS

MATERIAL
HOLDED PARTS: 94V-0 RATED
THERMOPLASTIC COLOR BLACK
CONTACTS: PH BRZ PER QQ-B-750

SIZE
CAGE CODE
DRAWING NO
RESTRICTED TO

TE Connectivity

KIT, AMP-LATCH PADDLEBOARD
PREASSEMBLED, .100 LONG POSTS
FULL ROW, FULL TIN PLATED CONTACTS

111035

SCALE 10:1
SHEET 1 OF 1
REV J

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[111035-3](#)