








RECOMMENDED HOLE LAYOUT

		1.950	1.950	2.274	1.950	1.950	39	40	5-111036-8
		.750	.750	1.074	.750	.750	15	16	5-111036-2
OBSOLETE		2.950	2.950	3.274	2.950	2.950	59	60	1-111036-3
OBSOLETE		2.750	2.750	3.074	2.750	2.750	55	56	1-111036-2
OBSOLETE		2.550	2.550	2.874	2.550	2.550	51	52	1-111036-1
OBSOLETE		2.350	2.350	2.674	2.350	2.350	47	48	1-111036-0
OBSOLETE		2.150	2.150	2.474	2.150	2.150	43	44	111036-9
		1.950	1.950	2.274	1.950	1.950	39	40	111036-8
OBSOLETE		1.750	1.750	2.074	1.750	1.750	35	36	111036-7
OBSOLETE		1.550	1.550	1.874	1.550	1.550	31	32	111036-6
OBSOLETE		1.350	1.350	1.674	1.350	1.350	27	28	111036-5
OBSOLETE		1.150	1.150	1.474	1.150	1.150	23	24	111036-4
OBSOLETE		.950	.950	1.274	.950	.950	19	20	111036-3
		.750	.750	1.074	.750	.750	15	16	111036-2
OBSOLETE		.550	.550	.874	.550	.550	11	12	111036-1
	FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN J. PEACHEY 05-MAR-86				TE Connectivity	
						CHK M.SCUILLY 23-MAY-86					
DIMENSIONS:						APP'D D.HOFFMAN 23-MAY-86		NAME			
INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC		KIT, AMP-LATCH PADDLEBOARD PREASSEMBLED, .156 LONG POSTS FULL ROW, FULL TIN PLATED CONTACTS			
		0 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ±				APPLICATION SPEC					
		FINISH				114-40005		SIZE		CAGE CODE	DRAWING NO
MATERIAL		CONTACTS				WEIGHT -		A1		00779	C=11036
HOLD PARTS: 94V-0 RATED UL RECOGNIZED: BLACK CONTACTS PH BRZ PER QQ-B-350		CUSTOMER DRAWING						SCALE		10:1	SHEET 1 of 1
											REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-111036-8](#)