





- 1 0.8 µm MIN AU OVER NICKEL
- 2 4 µm MIN Sn. OVER Cu UNDERLAYER
- 3 TIN PLATING
- 4 CD PLATED

-	THERMO PLASTIC	1	INSULATING PLATE	6
1	BRASS	20	PIN	5
2	BRASS	1	BRACKET	4
3	BRASS	1	RIVET	3
4	STEEL	1	RIVETING NUT	2
-	THERMO PLASTIC	2	INSULATING SLEEVE	1
FINISH	MATERIAL	Qty	PART DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.CORRIOU 15/04/1992		TE Connectivity				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME INSULATED BRACKET GROUNDING ASSY 20POS -				
		0 PLC ±						
		1 PLC ±						
		2 PLC ±0.13						
3 PLC ±		APVD Y.PETRONIN 11MARS2013		PRODUCT SPEC -				
4 PLC ±		APPLICATION SPEC						
ANGLES ±0°30'		-						
MATERIAL TABLE		FINISH TABLE		SIZE A 3		CAGE CODE 00779	DRAWING NO C-131618	RESTRICTED TO -
Customer Drawing				SCALE 5:2		SHEET 1 OF 1		REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[131618](#)