

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST



REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-16-009824	27JUL2016	GK	SD


REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2150656-1

FOR REPLACEMENT PARTS FOR APPLICATOR 1339522
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1339522

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GOPALAKRISHNA HV		 TE Connectivity			
		CHK	GOPALAKRISHNA HV					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		STOUGH DALE		END FEED HD-I APPLICATOR		
				PRODUCT SPEC				
				APPLICATION SPEC				
				WEIGHT				
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
				A3		©- 1339522		
CUSTOMER DRAWING				SCALE	SHEET 1 OF 2	REV	D1	

	VIEW B	ROTATED 180°
	POST-FEED 40 mm STROKE	POST-FEED 30 mm STROKE
		
LOC A		
DIST 66	LEADMAKER OR BENCH G	K TERMINATOR BENCH MACHINE



		-77 -71 -1		PART NO		DESCRIPTION		ITEM NO	
				← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)					
QTY REQD PER ASSY				PARTS LIST					
DIMENSIONS: mm [INCHES]				MATL		HT TR		FIN	
DO NOT SCALE PRINT.									
TOLERANCES UNLESS OTHERWISE SPECIFIED:				DR 14NOV001		APP 14NOV00			
1 PLC DEC ±-				M.C.LIFFORD		F.BACKHURST			
2 PLC DEC ±-				CHK -		REL 08-03-02			
3 PLC DEC ±-				-		M.C.LIFFORD			
ANGLES ±-				NAME		END FEED HD-I APPLICATOR		MACHINE REF	
SURF TEXTURE: ✓								HD-I I APPL	
REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX				SCALE -		DWG NO 1339522		SHEET 1 OF 1	
CASE CODE 00779				CUSTOMER AND ASSEMBLY DRAWING				REV D	
APP DATE								RESTRICTED TO -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1339522-1](#)