


 1. RECOMMENDED SPARE PARTS.

2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.


3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

 4. CUT TO LENGTH AT ASSY.

 5. CRIMP HEIGHTS CALCULATED SPECIFICALLY FOR DUTCH MARKET REQUIREMENTS.



					73
-	1	1	1339597	PRINT, APPLICATOR LOG SHEET	72
-	1	1	1338705-2	DOCUMENTATION PACKAGE	71
					70
					69
					68
-	1	1	461264-1	PLATE, IDENTIFICATION	67
-	2	2	21017-2	SCR,DRIVE (#2X.19) ID PLATE	66
					65
-	1	1	986950-1	WASHER, FLAT PRECISION	64
-	1	1	3-18031-0	SCR,SKT SET (M6X6)RAM	63
					62
					61
-	1	1	18024-7	SCR,BHC (M4X10) ANVIL	60
					59
					58
-	6	6	18023-9	SCR,SHC (M4X6) STRIP GUIDE	57
-	2	2	1-18023-2	SCR,SHC (M4X12) SLUG BLADE	56
					55
-	2	2	18029-1	NUT, HEX (M3) DRAG	54
-	2	2	986965-1	NUT,HEX SL (M4) DRAG STUD	53
-	2	2	2-18032-2	SCR,SKT SET (M3X10) DRAG	52
					51
					50
-	1	1	18024-3	SCR,BHC (M3X10) CAM	49
					48
-	1	1	1338676-1	CAM, POST-FEED 30 & 40 mm ST	47
-	1	1	1338662-1	APPLICATOR, BASIC (SUBA55Y)	46
-	1	1	690191-1	PLUG, NYLON	45
-	1	1	1320998-1	RAM	44
-	1	1	690125-1	WASHER, LAMINATED	43
-	1	1	690124-1	WASHER, RAM	42
-	1	1	2-18024-6	SCREW,BHC (M8X25) CRIMPER	41
					40
					39
-	1	1	690223-2	SPACER, INSULATION DISC	38
-	1	1	354777-1	WIRE DISC, PLASTIC	37
-	1	1	22480-5	WASHER, SPRING	36
-	1	1	690212-1	POST, RAM	35
					34
					33
-	8	8	18025-2	WASHER, LOCK (M4) SHEAR BL	32
-	2	2	1-18024-0	SCR,BHC (M4X20) SHEAR PL	31
					30
-	2	2	18024-8	SCR,BHC (M4X12) STRIPPER	29
-	1	1	3-690451-2	SPACER, STRIPPER	28
-	1	1	240639-1	STRIPPER	27
					26
-	2	2	1320906-1	DRAG, STUD	25
-	1	1	1320995-1	STRIP GUIDE	24
					23
-	2	2	4-22281-1	SPRING, DRAG	22
					21
-	1	1	1338665-1	DRAG, STOCK	20
-	2	2	1338664-1	GUIDE, UPPER STRIP	19
-	2	2	1338663-1	GUIDE, LOWER STRIP	18
-	4	4	1-18024-8	SCR,BHC (M6X12) STRIP GD PL	17
					16
					15
					14
					13
					12
-	1	1	240644-1	PLATE, REAR SHEAR	11
					10
-	1	1	690482-6	PLATE, FRONT SHEAR	9
1	2	1	1333224-2	ANVIL	8
-	1	1	690474-6	BLADE, SLUG	7
					6
-	1	1	1-240641-0	SPACER, SLUG BLADE	5
					4
					3
					2
1	2	1	456407-5	CRIMPER, WIRE	1
-77	-71	-1	PART NO	DESCRIPTION	ITEM NO
				← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)	

		-77-71 -1		PART NO		DESCRIPTION		ITEM NO											
				← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)															
QTY REQD PER ASSY										PARTS LIST									
		DIMENSIONS: mm (INCHES) DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ± 2 PLC DEC ± 3 PLC DEC ± ANGLES ± SURF TEXTURE: ✓				MATL -		HT TR		FIN -									
						DR 230CT01 L.L.OFHOUSE		APP 230CT01 F.BAKHURST		 AMP Incorporated Harrisburg, PA 17105-3608									
						CHK -		REL 20-11-01 M.CLIFFORD											
						NAME END FEED HD-I APPLICATOR				MACHINE REF HD-I APPL									
MC NOV01		REMOVE BURRS, BREAK				SCALE -		DWG NO		1339597		SHEET		REV					
APP DATE		RO.38 MAX				D						1 of 1		A					
		CAGE CODE 00779				CUSTOMER AND ASSEMBLY DRAWING								RESTRICTED TO -					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1339597-1](#)