





- △ HOUSING: HIGH TEMPERATURE, GLASS FILLED NYLON, COLOR: BLACK. CONTACTS: PHOSPHOR BRONZE.
- △ CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254 BRIGHT TIN-LEAD ON REMAINDER, ALL OVER 0.001270 NICKEL.
- △ NO CONTACT IN THIS POSITION, FOR PART NUMBER 1375963-1 & -3 ONLY.
- △ CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254-0.00508 MATTE TIN ON REMAINDER, ALL OVER 0.001270 NICKEL.
- △ ROHS 2002/95/EC COMPLIANT PART TO BE USED WITH ROHS 2002/95/EC COMPLIANT PCB'S.



△ 5	△ 4	NO	1375963-4
△ 5	△ 4	△ 3 YES	1375963-3
	△ 2	NO	1375963-2
	△ 2	△ 3 YES	1375963-1
FINISH		KEYED CIRCUITS	PART NO

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: W.G. LENKER 02JUN2000		EHW: L.BREKOSKY 15JAN2001		APVD: -		NAME: -		TE Connectivity	
mm	0 PLC ±	1 PLC ±0.01	2 PLC ±	3 PLC ±	4 PLC ±	PRODUCT SPEC: 108-1956		APPLICATION SPEC: 114-13021		WEIGHT: -		RESTRICTED TO: -	
MATERIAL: △		FINISH: △ 2 △ 4		CUSTOMER DRAWING		SCALE: 4:1		SHEET: 1 OF 1		REV: C1		ASSEMBLY, PC/104, NON-STACKTHROUGH CONTACTS, SOLDER SIZE: CAGE CODE DRAWING NO: A1 00779 C=1375963	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1375963-4](#)