






TERMINAL NAME: 2.54 KK, CRIMP TYPE SHROUDED											
AMP TERM PN		MFR TERM PN		MOLEX TERMINAL		AMP CRIMP SPECS					
1572150-1		08-50-0004		PAD LTR		CRIMP HEIGHT		WIRE SIZE			
1572150-2		08-55-0124		A		.032 ±.002 [0.81 ±0.05mm]		22			
				B		.030 ±.002 [0.76 ±0.05mm]		24			
				C		.029 ±.002 [0.74 ±0.05mm]		26			
				D		NOT		USED			
				CRIMP		SIZE	TYPE	RANGE			
				WIRE		.055 [1.40mm]	F	26-22			
				INSUL		.062 [1.57mm]	0	.062 MAX			
WIRE STRIP LENGTH		TERM APPL SPEC		FEED		APPL INSTRUCTION		SET UP GAGE		LAYOUT	
.115-.131		NONE		.350		408-8040		458637-1		L2713	
2	2	2	-	C		5-354779-8	PIN, WIRE DISC (.3280)C			129	
2	2	2	-	C		5-354779-7	PIN, WIRE DISC (.3275)B			127	
2	2	2	-	C		5-354779-3	PIN, WIRE DISC (.3255)A			126	
1	1	1	-	A		986950-1	WASHER, FLAT PRECISION			125	
1	1	1	-	A		217238-1	GENERAL INSTRUCTION PACKAGE			124	
1	1	1	-	-		4088040	SF APPL INST 408-8040			123	
										122	
1	1	1	-	A		4-21028-0	PIN,SLT SPR(ø.093x.75)ST 6DE PL			121	
REF	REF	REF	-	A		1-21030-1	PIN,DOWEL (ø.187x.50) LEVER			120	
REF	REF	REF	-	A		1-21030-6	PIN,DOWEL (ø.187x1.25)HOUSING			119	
REF	REF	REF	-	A		21045-3	RING,RET "C"(ø.187)FD FING PIN			118	
1	1	1	-	A		21024-5	WASHER, LOCK (#10)ADJ BLOCK			117	
REF	REF	REF	-	A		21024-5	WASHER,LOCK (#10)ADJ PLATE			116	
REF	REF	REF	-	A		21024-5	WASHER,LOCK (#10)FEED 6DE ROD			115	
2	2	2	-	A		21024-2	WASHER,LOCK (#4)FRONT STP GUIDE			114	
REF	REF	REF	-	A		5-21028-1	PIN,SLT SPR(ø.125x.50)ADJ ROD			113	
										112	
4	4	4	-	A		21024-4	WASHER, LOCK (#8) STRIPPER			111	
REF	REF	REF	-	A		21899-4	WASHER,FLAT (ø5/16) SCREW ADJ			110	
										109	
1	1	1	-	A		21018-5	NUT, HEX (NO. 6) HOLDDOWN			108	
REF	REF	REF	-	A		21068-5	NUT, HEX (6-32) FEED ADJ			107	
										106	
										105	
										104	
1	1	1	-	A		21009-2	SCR,SKT SET(1/4-20x.25 LW)RAM			103	
2	2	2	-	A		21017-2	SCR,DRIVE (#2x.19) ID PLATE			102	
REF	REF	REF	-	A		6-23715-5	SCR,PAN HD (6-32x1.50)FEED ADJ			101	
1	1	1	-	B		461264-1	PLATE, IDENTIFICATION			100	
2	2	2	-	A		3-21002-0	SCR,BHC (10-32x.88)DRAG			99	
1	1	1	-	A		22733-8	SCR,BHC (8-32x.38 LW)ANVIL			98	
REF	REF	REF	-	A		2-21002-9	SCR,BHC (10-32x.75)CAP			97	
REF	REF	REF	-	A		2-22733-8	SCR,BHC (1/4-20x.62)HOUSING			96	
REF	REF	REF	-	A		2-21002-7	SCR,BHC (10-32x.50)SG ADJ BLOCK			95	
6	6	6	-	A		2-21002-2	SCR,BHC (8-32x.50) TERM H DWN			94	
										93	
										92	
1	1	1	-	A		1-21002-7	SCR,BHC (6-32x.38)CAM			91	
										90	
										89	
										88	
2	2	2	-	A		9-21000-9	SCR,SHC (8-32x.44)DEP-HOLD			87	
1	1	1	-	A		2-22603-0	SCR,HEX HD (8-32x.31)FEED FINGER			86	
2	2	2	-	A		1-21000-3	SCR,SHC (4-40x.25)FR ST GUIDE			85	
1	1	1	-	A		2-21000-7	SCR,SHC (8-32x.50)STRIPPER			84	
REF	REF	REF	-	A		3-21000-7	SCR,SHC (10-32x.75)FEED ROD 6D			83	
REF	REF	REF	-	A		3-21000-6	SCR,SHC (10-32x.62)FD ADJ BLK			82	
1	1	1	-	A		3-21000-4	SCR,SHC (10-32x.38)SG ADJ BL			81	
REF	REF	REF	-	A		3-21000-4	SCR,SHC (10-32x.38)PIVOT BLK			80	
-	REF	-	-	B		455749-1	GUARD, WINDOW			79	
REF	-	-	-	B		679532-1	INSERT, GUARD			78	
										77	
										76	
										75	
1	1	1	-	A		690603-1	SPRING, ASSIST			74	
1	1	1	-	A		23030-1	SCR,SHC (6-32x.25 SL)INS DISC			73	
REF	REF	REF	-	A		458109-1	WASHER, SPECIAL			72	
REF	REF	REF	-	A		690517-1	SPACER			71	
-3	-2	-1	U/M	DWG SIZE		PART NO	DESCRIPTION			ITEM NO	
QTY RECD PER ASSY				PARTS LIST							
											
							B	ECR 05-003707	TE		
							A1	0150-0254-03	CE		
							A	RELEASED	GB		
				P	F	LTR	REVISION RECORD		APP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385480-1](#)