

4

3

2


1

D

C

B

A



RP78601

RP78602

PART NO:		PART NAME:		MATERIAL/SURFACE:		OPTIONAL DESCRIPTION	
PART LIST							
TOLERANCES UNLESS OTHERWISE SPECIFIED ACCORDING TO ISO 8015 and ISO 2768-m						DIMENSIONS: mm	
test dimen. / Prüfmaß: ; auxiliary dimen. / Hilfsmaß: (  ); theor. dimen. / theor. Maß: ; production control dimen. / Fertigungskontrollmaß: [  ]; dimen. for measure. technology / messtechn. rel. Maß: ] [  ;							
				DEPARTMENT			
				DRAWER			
				CHECKED			
				APPROVED			
ECO-11-005027		19APR11		HMR		TE Connectivity	
ECO-NO.:		DATE		NAME		INFO	
SCALE:		NAME:				DWG NO.:	
-				RT Print-Socket		1393234	
						OPTIONAL NO.:	
						RP78601--/01	
REPLACEMENT FOR:				DWG LOC NO.: IF		SHEET: OF	
						REVISION: A2	
						A 4	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RP78601](#)