

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	ECR-14-010131	18AUG2014	GK	HMR

REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2266335-1


FOR REPLACEMENT PARTS FOR APPLICATOR 1426179
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1426179

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV		 TE Connectivity	
DIMENSIONS:		CHK RAGHAVENDRA			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RAGHAVENDRA	
		0 PLC ±		NAME SIDE FEED HD-I APPLICATOR	
		1 PLC ±		PRODUCT SPEC	
MATERIAL		2 PLC ±		APPLICATION SPEC	
		3 PLC ±		SIZE A3	
FINISH		4 PLC ±		CAGE CODE	
		ANGLES ±		DRAWING NO C- 1426179	
		WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE	
				SHEET 1 OF 2	
				REV C1	



1. RECOMMENDED SPARE PARTS.
2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.
3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.
4. CUT TO LENGTH AT ASSY.
5. HOLD DOWN AND TERMINAL SUPPORT NOT REQUIRED FOR SOCKET. REPOSITION WHEN USED FOR PIN VERSION.



QTY		REQD PER Assy		PARTS LIST			
DIMENSIONS: mm (INCHES)				MATL		HT TR	
DO NOT SCALE PRINT.				-		FIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED,				DR		21MAR01	
1 PLC DEC ± 0.5 (.02 IN)				L.L.OFHOUSE		F.BACKHURST	
3 PLC DEC $\pm$				CHK -		REL 21MAR01	
3 PLC DEC $\pm$						L.L.OFHOUSE	
ANGLES $\pm$				NAME		MACHINE REF	
SURF TEXTURE, $\checkmark$				SIDE FEED HD-I APPLICATOR		HD-I APPL	
REMOVE BURRS, BREAK SHARP EDGES $\pm .03$ MAX				SCALE		DWG NO	
				1		1426179	
CASE CODE				SHEET			
00779				1 OF 1			
CUSTOMER AND ASSEMBLY DRAWING				REV			
				C			
				RESTRICTED TO			
				-			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426179-6](#)