

 1. RECOMMENDED SPARE PARTS.

2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.

3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.



QTY REQD PER ASSY				PARTS LIST			
DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ± 0.5 [0.02 IN] 2 PLC DEC $\pm$ - 3 PLC DEC $\pm$ - ANGLES $\pm$ - SURF TEXTURE: $\checkmark$ REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX				MATL - HT TR - FIN - DR 26MAR01 APP 26MAR01 F.BACKHURST CHK - REL 10MAY01 L.LOFTHOUSE AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME SIDE FEED HD-I APPLICATOR MACHINE REF HD-I APPL SCALE - D DWG NO 1426185 SHEET 1 OF 1 REV C CASE CODE 00779 CUSTOMER AND ASSEMBLY DRAWING RESTRICTED TO -			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426185-6](#)