


										73
-	1	1	1	1	1	1	1	1426268	PRINT, APPLICATOR LOG SHEET	72
-	1	1	1	1	1	1	1	1338705-1	DOCUMENTATION PACKAGE	71
										70
										69
										68
-	1	1	1	1	1	1	1	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	2	2	2	21017-2	SCR,DRIVE (#2x.19) ID PLATE	66
										65
-	1	1	1	1	1	1	1	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	1	1	1	3-18031-0	SCR, SKT SET (M6X6) RAM	63
-	1	1	1	1	1	1	1	18023-9	SCR,SHC (M4X6) INS DISC	62
-	2	2	2	2	2	2	2	2-18032-5	SCR, SKT SET (M5X20) DRAG	61
-	1	1	1	1	1	1	1	18024-7	SCR,BHC (M4X10) ANVIL	60
-	1	1	1	1	1	1	1	5-18022-2	SCR, HEX (M4X8) FEED FINGER	59


									58
-	1	1	1	1	1	1	1338685-1	PAWL, FEED	57
									56
									55
-	4	4	4	4	4	4	18024-8	SCR,BHC (M4x12) SHEAR HOLDER	54
									53
-	1	1	1	1	1	1	18030-1	NUT, HEX (M3) HOLD DOWN	52
-	1	1	1	1	1	1	811242-5	BUMPER, HOLDDOWN	51
-	1	1	1	1	1	1	690753-2	SPACER, TONKER	50
-	1	1	1	1	1	1	18024-3	SCR,BHC (M3X10) CAM	49
-	-	1	-	-	1	-	1338675-1	CAM, PRE FEED 30 & 40 mm ST	48
-	1	-	1	1	-	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	47
-	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	46
-	1	1	1	1	1	1	690191-1	PLUG, NYLON	45
-	1	1	1	1	1	1	1338660-1	RAM	44

-	1	1	1	1	1	1	690125-1	WASHER, LAMINATED	43
-	1	1	1	1	1	1	690124-1	WASHER, RAM	42
-	1	1	1	1	1	1	2-18024-6	SCR,BHC (M8X25) RAM	41
-	1	1	1	1	1	1	23241-1	BALL, STEEL	40
-	1	1	1	1	1	1	2-22278-7	SPRING, COMPRESSION	39
-	1	1	1	1	1	1	1320922-1	DISC, INSULATION	38
-	1	1	1	1	1	1	354777-1	WIRE DISC, PLASTIC	37
-	1	1	1	1	1	1	22480-5	WASHER, SPRING	36
-	1	1	1	1	1	1	690212-1	POST, RAM	35
-	1	1	1	1	1	1	1320934-1	SUPPORT, TERMINAL	34
-	2	2	2	2	2	2	1-18024-0	SCR,BHC (M4X20) STRIP GUIDE	33
-	1	1	1	1	1	1	18027-2	WASHER, FLAT (M4)	32
-	3	3	3	3	3	3	1-18023-2	SCR,SKT CAP (M4X12) MOUNT BLOCK	31
-	1	1	1	1	1	1	1320908-1	SPACER, STRIP GUIDE	30
-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29


[illegible]

	-	1	1	1	1	1	1	3-22280-3	SPRING, SHEAR	ITEM NO 13
	-	1	1	1	1	1	1	356885-4	STOP, SHEAR	12
	-	-	1	1	-	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	11
	-	1	1	1	1	1	1	462006-1	SHEAR, FLOAT (FRONT)	10
	1	2	2	2	1	1	1	2-1333203-3	ANVIL	9
										8
										7
										6
	-	1	1	1	1	1	1	2-455889-0	DEPRESSOR, SHEAR (FRONT)	5
	-	1	1	1	1	1	1	238011-7	SPACER, BLOCK CRIMPER	4
	1	2	2	2	1	1	1	1424909-6	CRIMPER, INSULATION	3
	-	1	1	1	1	1	1	455888-9	SPACER, CRIMPER	2
	1	2	2	2	1	1	1	4-456404-7	CRIMPER, WIRE	1
-77	-76	-72	-71	-6	-2	-1		PART NO	DESCRIPTION	ITEM NO
								REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)		

QTY REQD PER ASSY				PARTS LIST			
DIMENSIONS: mm [INCHES]		MATL		HT TR		FIN	
DO NOT SCALE PRINT.		-		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 13NOV01		APP 13NOV01			
1 P/LC DEC ±0.5 [0.02 IN]		L.L.OFTHOUSE		F.BACKHURST			
2 P/LC DEC ±		CHK -		REL 14-12-01		 AMP Incorporated Harrisburg, PA 17105-3608	
3 P/LC DEC ±		-		L.L.OFTHOUSE			
ANGLES ±		NAME				MACHINE REF	
SURF TEXTURE: ✓		SIDE FEED HD-I APPLICATOR				HD-I APPL	
REMOVE BURRS, BREAK		SCALE		DWG NO		SHEET	
SHARP EDGES R0.38 MAX		-		D 1426268		1 OF 1	
RK APP		APROB DATE				REV C	



		C	ECR-06-009199	RK	APROB	
P	F	LTR	REVISION RECORD	APP	DATE	

DIMENSIONS: mm [INCHES]		MATL		HT TR		FIN	
DO NOT SCALE PRINT.		-		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 13NOV01		APP 13NOV01			
1 PLC DEC ±.0.5 [.02 IN]		L.L.FOHOUSE		F. BACKHURST		 AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ±.		CHK -		REL 14-12-01			
3 PLC DEC ±.				L.FOHOUSE			
ANGLES ±.		NAME		SIDE FEED HD-1 APPLICATOR			MACHINE
SURF TEXTURE: ✓							HD-1
REMOVE BURRS, BREAK SHARP EDGES R0.38 MAX		SCALE		DWG NO		SHEET	
		-		1426268		1 of 1	
		D				REV	
						C	

THIS DRAWING IS UNPUBLISHED.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426268-1](#)