

AMP 1756 REV 3-92	12-DEC-03	14:07:04 us016926	7	6
-------------------	-----------	-------------------	---	---



QTY READ PER ASSY				PARTS LIST					
		DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ± 2 PLC DEC ± 3 PLC DEC ± ANGLES ± ° SURF TEXTURE: ✓		MATL	—	HT TR	—	FIN	—
				DR 27FEB02 M.CLIFFORD	APP 27FEB02 F.BACKHURST	 AMP Incorporated Harrisburg, PA 17105-3608			
				CHK —	REL 22-04-02 M.CLIFFORD				
				NAME SIDE FEED HD-I APPLICATOR			MACHINE REF HD-I APPL		
TE	12-03			SCALE —	DWG NO	1426294		SHEET 1 of 1	REV B
MC	APRO2	REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX							
APP	DATE			CASE CODE 00779					RESTRICTED TO —
CUSTOMER AND ASSEMBLY DRAWING									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426294-6](#)