


VIEW B ROTATED 180°

POST FEED 40 mm STROKE	POST FEED 30 mm STROKE	PRE FEED 30 mm STROKE	PRE FEED 40 mm STROKE

LOC
A
DIST
66

(44) (REF)
 (47)
 (49)



QTY READ PER ASSY				PARTS LIST			
DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ± 2 PLC DEC ± 3 PLC DEC ± ANGLES ± SURF TEXTURE: ✓ REMOVE BURRS, BREAK SHARP EDGES RO. 38 MAX				MATL — DR 09JUN03 L.L.LOFTHOUSE CHK —		HT TR — APP 09JUN03 F.BACKHURST REL 18JUL03 L.L.LOFTHOUSE	
						Tyco Electronics Harrisburg, PA 17105-3608	
RK	JAN06			NAME SIDE FEED HD-I APPLICATOR		MACHINE REF HD-I APPL	
LJL	JUL03			SCALE —	 DWG NO 1426443	SHEET 1 OF 1	REV B
APP	DATE	CASE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING			
				RESTRICTED TO —			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426443-6](#)