







	-	1	1	1	1	1	1	1426482	PRINT, APPLICATOR LOG SHEET	73
	-	1	1	1	1	1	1	1338705-1	DOCUMENTATION PACKAGE	72
										71
										70
										69
	-	1	1	1	1	1	1	461264-1	PLATE, IDENTIFICATION	68
	-	2	2	2	2	2	2	21017-2	SCR,DRIVE (#2x.19) ID PLATE	67
										66
	-	1	1	1	1	1	1	986950-1	WASHER, FLAT PRECISION	65
	-	1	1	1	1	1	1	3-18031-0	SCR,SKT SET (M6X6) RAM	64
	-	1	1	1	1	1	1	18023-9	SCR,SHC (M4X6) INS DISC	63
	-	2	2	2	2	2	2	2-18032-5	SCR.SET (M5X20) DRAG	62
	-	1	1	1	1	1	1	18024-7	SCR,BHC (M4X10) ANVIL	61
	-	1	1	1	1	1	1	5-18022-2	SCR,HEX (M4X8)FEED FINGER	60
										59
										58
	-	1	1	1	1	1	1	1338685-1	PAWL, FEED	57
										56
	-	2	2	2	2	2	2	18024-8	SCR,BHC (M4x12)SHEAR HOLDER	55
										54
										53
										52
										51
	-	1	1	1	1	1	1	18024-3	SCR,BHC (M3X10) CAM	50
	-	-	1	-	-	1	-	1338675-1	CAM, PRE FEED 30 & 40 mm ST	49
	-	1	-	1	1	-	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	48
	-	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	47
	-	1	1	1	1	1	1	690191-1	PLUG, NYLON	46
	-	1	1	1	1	1	1	1338660-3	RAM	45
	-	1	1	1	1	1	1	690125-1	WASHER, LAMINATED	44
	-	1	1	1	1	1	1	690124-1	WASHER, RAM	43
	-	1	1	1	1	1	1	2-18024-6	SCR,BHC (M8X25) RAM	42
	-	1	1	1	1	1	1	23241-1	BALL, STEEL	41
	-	1	1	1	1	1	1	2-22278-7	SPRING, COMPRESSION	40
	-	1	1	1	1	1	1	1320922-1	DISC, INSULATION	39
	-	1	1	1	1	1	1	354777-1	WIRE DISC, PLASTIC	38
	-	1	1	1	1	1	1	22480-5	WASHER, SPRING	37
	-	1	1	1	1	1	1	690212-1	POST, RAM	36
										35
	-	2	2	2	2	2	2	1-18024-0	SCR,BHC (M4X20)STRIP GUIDE	34
	-	1	1	1	1	1	1	18027-2	WASHER, FLAT (M4)	33
	-	1	1	1	1	1	1	1-18023-2	SCR,SKT CAP (M4X12)MOUNT BLOCK	32
	-	1	1	1	1	1	1	1320908-4	SPACER, STRIP GUIDE	31
	-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	30
										29
	-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	28
	-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	27
	-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	26
	-	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	25
	-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	24
	-	1	-	1	1	-	1	690472-2	STRIPPER	23
	-	1	1	1	1	1	1	1-18023-1	SCR,SHC (M4X10)STRIPPER	22
	-	1	1	1	1	1	1	18025-2	WASHER,LOCK (M4)STRIPPER	21
	-	-	1	-	-	1	-	690472-1	STRIPPER	20

QTY REQD PER ASSY				PARTS LIST			
TM MC APP	DECOR APPRO DATE	DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT.		MATL	HT TR	FIN	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR	17FEB04	APP	17FEB04
		1 PLC DEC ± -		L.L.OFHOUSE		F. BACKHURST	
		2 PLC DEC ± -		CHK		REL	06-04-04
		3 PLC DEC ± -				M. CLIFFORD	
ANGLES ± -		NAME		SIDE FEED HD-I APPLICATOR		MACHINE	REF
SURF TEXTURE: ✓		SCALE		D		DWG NO	1426482
REMOVE BURRS, BREAK SHARP EDGES R. 38 MAX						SHEET	REV
						1 of 1	B
CASE CODE		00779				CUSTOMER AND ASSEMBLY DRAWING	
						RESTRICTED TO	
						-	

THIS DRAWING IS UNPUBLISHED.  
© COPYRIGHT 20

3



GUIDE OFF  
INSULATION BARREL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426482-1](#)